


ME 22,5 TBUS 1,5/ 5-ST-3,81 YE - 1PCS - DIN rail  
bus connector



1225375  
<https://www.phoenixcontact.com/ae/products/1225375>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail bus connector, nominal current: 8 A (parallel contacts), rated voltage (III/2): 125 V, number of positions: 5, pitch: 3.81 mm, color: yellow, mounting: DIN rail, item with gold-plated contacts, bus connector for connecting to electronics housings, 5 parallel contacts

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1225375       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DNA           |
| Product key                          | DNA366        |
| GTIN                                 | 4063151317461 |
| Weight per piece (including packing) | 8.4 g         |
| Weight per piece (excluding packing) | 8 g           |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# ME 22,5 TBUS 1,5/ 5-ST-3,81 YE - 1PCS - DIN rail bus connector



1225375

<https://www.phoenixcontact.com/ae/products/1225375>

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Product properties

|                     |                        |
|---------------------|------------------------|
| Product type        | DIN rail bus connector |
| Number of positions | 5                      |
| Pitch               | 3.81 mm                |

### Material specifications

|                                        |                   |
|----------------------------------------|-------------------|
| Color (Housing)                        | yellow (RAL 1018) |
| Flammability rating according to UL 94 | V0                |
| Insulating material                    | PA                |
| Housing material                       | PA                |

### Dimensions

|       |         |
|-------|---------|
| Width | 22.5 mm |
| Pitch | 3.81 mm |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                         |                   |
|-----------------------------------------|-------------------|
| Ambient temperature (operation)         | -40 °C ... 105 °C |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C  |
| Ambient temperature (assembly)          | -5 °C ... 100 °C  |

# ME 22,5 TBUS 1,5/ 5-ST-3,81 YE - 1PCS - DIN rail bus connector



1225375

<https://www.phoenixcontact.com/ae/products/1225375>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460202 |
| ECLASS-15.0 | 27460202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002638 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# ME 22,5 TBUS 1,5/ 5-ST-3,81 YE - 1PCS - DIN rail bus connector



1225375

<https://www.phoenixcontact.com/ae/products/1225375>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Middle East FZ LLC  
1201N-1206N, Dubai Science Park Towers – North  
P.O. Box 345002, Dubai, United Arab Emirates  
(+971) 4 437-0324  
[info-me@phoenixcontact.com](mailto:info-me@phoenixcontact.com)