


PART NUMBER	TITLE	CABLE DESCRIPTION	LENGTH 'L'	CABLE COLOR
2153481121	Squba 3.6 M-S 75mm 16 AWG leads BK Sn	1X16AWG DISC MPPE BK UL11028 HKUP	75±3	BLACK
2153481122	Squba 3.6 M-S 150mm 16 AWG leads BK Sn	1X16AWG DISC MPPE BK UL11028 HKUP	150±5	BLACK
2153481123	Squba 3.6 M-S 225mm 16 AWG leads BK Sn	1X16AWG DISC MPPE BK UL11028 HKUP	225±5	BLACK
2153481124	Squba 3.6 M-S 300mm 16 AWG leads BK Sn	1X16AWG DISC MPPE BK UL11028 HKUP	300±5	BLACK
2153481125	Squba 3.6 M-S 450mm 16 AWG leads BK Sn	1X16AWG DISC MPPE BK UL11028 HKUP	450±5	BLACK
2153482121	Squba 3.6 M-S 75mm 16 AWG leads RD Sn	1X16AWG DISC MPPE RD UL11028 HKUP	75±3	RED
2153482122	Squba 3.6 M-S 150mm 16 AWG leads RD Sn	1X16AWG DISC MPPE RD UL11028 HKUP	150±5	RED
2153482123	Squba 3.6 M-S 225mm 16 AWG leads RD Sn	1X16AWG DISC MPPE RD UL11028 HKUP	225±5	RED
2153482124	Squba 3.6 M-S 300mm 16 AWG leads RD Sn	1X16AWG DISC MPPE RD UL11028 HKUP	300±5	RED
2153482125	Squba 3.6 M-S 450mm 16 AWG leads RD Sn	1X16AWG DISC MPPE RD UL11028 HKUP	450±5	RED



ITEM	PART#	DESCRIPTION	QTY	UOM
A	2077760001	Squba 3.6 male terminal 16 AWG	1	PC

- NOTES:
1. Crimping to be done as per Molex standards.
  2. The product specification relies on the terminals & wire spec.
  3. Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 1.9mm Max.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2021/05/27	A	INITIAL RELEASE	AS20

DOCUMENT STATUS	P1	RELEASE DATE	2021/05/31	12:34:17
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS FA = 0 FE = 0 FP = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		<b>molex</b>
	DIMENSION UNITS	SCALE	GENERAL TOLERANCES (UNLESS SPECIFIED)		
DIVISIONAL SYMBOLS	mm	NTS	ANGULAR TOL ± °		EC NO: 665606 DRWN: AS20 2021/05/27 CHK'D: RDESAI01 2021/05/31 APPR: RDESAI01 2021/05/31
	4 PLACES	±	3 PLACES ±		
	3 PLACES	±	2 PLACES ±		
	2 PLACES	±	1 PLACE ±		
	1 PLACE	±	0 PLACES ±		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	DOCUMENT NUMBER
			A4-SIZE	215348	2153481121
					DOC TYPE
					PSD
					DOC PART
					000
					REVISION
					A
					MATERIAL NUMBER
					SEE TABLE
					CUSTOMER
					GENERAL MARKET
					SHEET NUMBER
					1 OF 1