

Part Number : [347910181](#)

Product Description : Mini50 Unsealed Receptacle, Single Row, Bridged, 8 Circuits, Polarization Option B, Gray

Series Number : 34791

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[347910181_sd.pdf](#)

[PK-31301-538-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-34791-020-CH-001.pdf](#)

[AS-34791-020-001.pdf](#)

[AS-34791-020-CH-001.pdf](#)

[AS-34791-020-FR-001.pdf](#)

[PS-34791-020-001.pdf](#)

[347910020-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	34791
Description	Mini50 Unsealed Receptacle, Single Row, Bridged, 8 Circuits, Polarization Option B, Gray
Application	Automotive, Wire-to-Board
Component Type	Receptacle
Product Name	Mini50
UPC	887191319841

Physical

Circuits (maximum)	8
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	1.392/g

Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarization	B
Polarized to Mating Part	Yes
Sealed	Unsealed
Stackable	No
Temperature Range - Operating	-40° to +105°C
Terminal Size	0.5

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Vertical Headers	<u>34792</u>
Mini50 Unsealed Right-Angle Headers	<u>34793</u>
Mini50 Unsealed Single Row Right-Angle Headers	<u>34912</u>
Mini50 Unsealed Single Row Inline Housings	<u>203700</u>

Use with Part(s)

Description	Part Number
CTX50 Unsealed Receptacle Terminals	<u>560023</u>

This document was generated on Sep 02, 2026