Data sheet

TS 35X7.5 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Similar to illustration

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm
Order No.	9300090000
Type	TS 35X7.5 2M/ST/SZ
GTIN (EAN)	4032248387564
Qty.	40 M

Downloaded from Arrow.com.

Data sheet

TS 35X7.5 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	350 g		

Temperatures

Ambient temperature	-5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Mounting rail

Installation advice	Direct mounting	
Standards	DIN EN 60715	
Surface finish	galvanic zinc plated and passivated	
Thickness	1.00 mm	
Basic material	Steel	
Length of the terminal rail	min.	0 mm
	nominal	2000 mm
	max.	2000 mm
Short-time withstand current per second according to IEC 60947-7-2	1.92 kA	
Pre-punched mounting rail	No	
Slit width		
Short circuit strength corresponds to E-Cu wire	16.00 mm²	
Spacing of holes, centre-to-centre	0 mm	
Slit gap		
Slit length		

Important note

Product information	Din rails with Sendzimier treatment have limited corrosion resistance on the outer and cut edges

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

Downloaded from Arrow.com.


TS 35X7.5 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Product image



Downloaded from Arrow.com.