

15-Pin SATA (Female) to 4-Pin (Male) Power Cable - 26 AWG, 6-in. (15.24 cm)

MODEL NUMBER: **P944-06I**



15-pin SATA (Female) to 4-Pin (Male) cable powers a Serial ATA hard drive from a standard Molex connection.

Features

15-Pin SATA to 4-Pin Molex Power Cable Needs Only an LP4 Power Supply Connection This SATA 15-pin to 4-pin power cable connects any Serial ATA drive to any conventional LP4 internal connector. Ideal for desktops or servers equipped with a 2.5 in. or 3.5 in. SATA hard drive, this six-inch cable features one 4-pin Molex (LP4) male connector and one 15-pin SATA female power connector. It eliminates the need to upgrade the computer power supply for compatibility with newer SATA drives. The LP4 male pass through connector prevents having to take up a connector on the SATA drive.

Highlights

- Connects a SATA drive's 15-pin power port to a standard internal 4-pin Molex power supply
- Compatible with 2.5 in. and 3.5 in. SATA drives
- 4-Pin (Male) connector is pass through to avoid taking up a power supply connector

Applications

- Use power from your computer via its LP4 connection to operate your SATA drive with a desktop computer or server containing multiple drives

Package Includes

- P944-06I 15-Pin SATA (Female) to 4-Pin (Male) Power Cable, 6-in. (15.24 cm)

Specifications

OVERVIEW	
UPC Code	037332117779
Technology	SATA/eSATA
Country/Region	Global
INPUT	
Maximum Input Amps	0
PHYSICAL	
Color	Black; Red; Yellow
Number of Conductors	0
Wire Gauge (OD - mm ²)	0
Cable Length (ft.)	0.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
Power Cord Jacket Type	Null
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.14
CONNECTIONS	
Side A - Connector 1	15 PIN SATA POWER (FEMALE)
Side B - Connector 1	4 PIN (MALE)
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
STANDARDS & COMPLIANCE	
Certifications	ROHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>