

Protect It! 230V Surge Protector with 6 French/Belgian Outlets, 2M Cord, 1140 Joules, French plug

MODEL NUMBER: **TLP61F**



Highlights

- 6 safety outlet covers
- 2 m cord
- "Protected" LED
- 1140 joule rating

Package Includes

- TLP61F surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP61F offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP61F offers 6 French Type E outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP61F offers economical AC surge suppression
- 1140 joules AC surge suppression shields equipment from surges and line noise
- 6 French Type E outlets protects computers and peripherals
- 2 m cord with French plug
- Protected LED
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145444
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	French
Input Cord Length (ft.)	6

Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(6) French/Belgian
Circuit Breaker (amps)	10
Transformer Accommodation	(3) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green Protected
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1140
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Light Gray
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	No
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	18.20 x 1.75 x 4.80
Shipping Dimensions (hwd / cm)	46.23 x 4.44 x 12.19
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
Unit Dimensions (hwd / in.)	16.000 x 2.320 x 1.750
Unit Dimensions (hwd / cm)	40.64 x 5.89 x 4.45
Unit Weight (lbs.)	1.2
Unit Weight (kg)	0.54
FEATURES & SPECIFICATIONS	



Powering Business Worldwide

TRIPP-LITE
by **EATON**

Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.