Part Number : 936013138
Product Description : Heavy-Duty High Performance-Harsh Environment (HP-HE) Bulkhead Housing, Screw Locking, Zinc Alloy, Top Entry, Size 24B «104x27», Black
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7824.3738.3



Documents and Resources

Drawings

936013138_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per ED/71/2019 (16 July 2019)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty High Performance-Harsh Environment (HP-HE) Bulkhead Housing, Screw Locking, Zinc Alloy, Top Entry, Size 24B «104x27», Black
Comments	Screw Locking
Component Type	Bulkhead Mount Housing
IP Rating	IP68, IP69
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191873015

Physical

Component Size	24B «104X27»
Entry Location	Top
Housing Coating	Epoxy-Polyester Powder
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Housing	Zinc Alloy

Downloaded from Arrow.com.

Net Weight	185.800/g
Packaging Type	Bag
Thread Size	N/A
Thread Type	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 24 «104x27» S-D, S-DD, S-E, S-ES, S-EP, S-E, S-EEE, S-HSB, S-K, andS-M Inserts

Downloaded from Arrow.com.