

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 42U, without Sides, Black, 2258H x 750W x 1070D mm

AR3150X609

### Overview

|              |                                                                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | Wide enclosure with increased cable management options for high density server and networking applications. 42U height to easily roll through doorways. |
| Lead time    | Usually in Stock                                                                                                                                        |

### Main

|                           |                                                                                                    |
|---------------------------|----------------------------------------------------------------------------------------------------|
| Product or component type | Rack enclosure                                                                                     |
| Number of rack unit       | 42U                                                                                                |
| Provided equipment        | Baying hardware<br>Casters<br>Door key<br>Doors<br>Leveling feet<br>Rack mounting hardware<br>Roof |

### Physical

|                            |                                                                                                           |
|----------------------------|-----------------------------------------------------------------------------------------------------------|
| Height                     | 199.14 cm                                                                                                 |
| Width                      | 75 cm                                                                                                     |
| Depth                      | 107 cm                                                                                                    |
| Net weight                 | 126.86 kg                                                                                                 |
| Colour                     | Black                                                                                                     |
| Mounting preference        | No preference                                                                                             |
| Mounting mode              | Not rack-mountable                                                                                        |
| Mounting location          | Front                                                                                                     |
| Maximum mounting depth     | 91.49 cm                                                                                                  |
| minimum mounting depth     | 26.19 cm                                                                                                  |
| Rack width                 | 19"                                                                                                       |
| Marking                    | 14 gauge EIA mounting rail<br>16 gauge front door<br>16 gauge post<br>16 gauge rear door<br>18 gauge roof |
| Permanent permissible load | 1020.6 kg dynamic<br>1360.8 kg static                                                                     |

### Conformance

|           |                                   |
|-----------|-----------------------------------|
| Standards | UL 2416<br>UL 60950-1<br>EIA-310E |
|-----------|-----------------------------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 221.6 cm  |
| Package 1 Width              | 121.9 cm  |
| Package 1 Length             | 89.5 cm   |
| Package 1 Weight             | 139.09 kg |

## Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained](#) >

[How we assess product sustainability](#) >

Use Better

|  Materials and Substances |                                                            |
|------------------------------------------------------------------------------------------------------------|------------------------------------------------------------|
| Packaging made with recycled cardboard                                                                     | No                                                         |
| Packaging without single use plastic                                                                       | No                                                         |
| <a href="#">EU RoHS Directive</a>                                                                          | Pro-active compliance (Product out of EU RoHS legal scope) |
| REACH Regulation                                                                                           | <a href="#">REACH Declaration</a>                          |

Use Again

|  Repack and remanufacture |                                         |
|------------------------------------------------------------------------------------------------------------|-----------------------------------------|
| Circularity Profile                                                                                        | <a href="#">End of Life Information</a> |
| Take-back                                                                                                  | Yes                                     |