

Product data sheet

Subminiature connectors




Product description	M9 Female panel mount connector, Contacts: 5, unshielded, solder, IP67, M12x0.5, Front mounting
Area	M9 IP67
Series	712
Part no.	09 0416 00 05


Illustration



Scale drawing



Contact arrangement (Plug-in side)



You can find the component part drawing and assembly instructions on the next page.

Technical data

General features

Part no.	09 0416 00 05
Connector design	Female panel mount connector
Version	Connector socket straight
Connector locking system	screw
Termination	solder
Degree of protection	IP67
Connection cross-section	0.25 mm² / AWG 24
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 500 Mating cycles
Weight (g)	5.27
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	125 V
Rated impulse voltage	1500 V
Rated current	3,0 A
Insulation resistance	≥ 10 ⁸ Ω
Pollution degree	1
Overvoltage category	II
Insulating material group	III
EMC compliance	unshielded

Product data sheet

Subminiature connectors



Product description	M9 Female panel mount connector, Contacts: 5, unshielded, solder, IP67, M12x0.5, Front mounting
Area	M9 IP67
Series	712
Part no.	09 0416 00 05

Material

Contact body material	PA (UL94 V-0)
Contact material	CuSn (bronze)
Contact plating	Au (gold)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	1327cde4-6524-4488-a984-39e100d57919

Classifications


eCl@ss 11.1	27-44-01-09
ETIM 9.0	EC003569

Trade-Compliance

Copper (9903.78.01)	0.002205 kg
---------------------	-------------

Product description	M9 Female panel mount connector, Contacts: 5, unshielded, solder, IP67, M12x0.5, Front mounting
Area	M9 IP67
Series	712
Part no.	09 0416 00 05

Assembly instructions / Panel cut-out




Product data sheet

Subminiature connectors



Product description	M9 Female panel mount connector, Contacts: 5, unshielded, solder, IP67, M12x0.5, Front mounting
Area	M9 IP67
Series	712
Part no.	09 0416 00 05

Component part drawing



Product data sheet

Subminiature connectors



Product description	M9 Female panel mount connector, Contacts: 5, unshielded, solder, IP67, M12x0.5, Front mounting
Area	M9 IP67
Series	712
Part no.	09 0416 00 05

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.