

## 48-Port 1U Rack-Mount High-Density UTP 110-Type Patch Panel, RJ45 Ethernet, 568B, Cat5/5e, TAA

MODEL NUMBER: **N052-048-1U**



Saves rack space by managing and organizing up to 48 input and output Cat5/5e network cable connections in just 1U of EIA-standard 19 in. rack.

### Description

The N052-048-1U 48-Port 1U Rack-Mount High-Density 110-Type Patch Panel frees up valuable real estate by condensing 48 ports into just 1U of space in your EIA-standard 19-inch rack. Made from heavy-duty 14ga cold-rolled steel, this patch panel includes a built-in cable-management loom that keeps cables efficiently organized on the back of the panel.

The N052-048-1U is specially designed for easy punchdown termination. Just remove four screws to take off the upper deck, punch down the lower cables, replace the upper deck, and punch down the upper cables. Ports are clearly numbered to help you identify connections and color-coded for 568A/B wiring. Includes 48 nylon cable ties. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. Meets ANSI/TIA-568-C.2, ISO/IEC 11801 and IEC 60603-7 standards.  
UTP Cat5e 22-24 AWG Solid Cable

### Features

#### Condenses 48 Ports into Just 1U of Rack Space

- Ports are numbered and color-coded for easy identification
- Heavy-duty 14ga cold-rolled steel construction
- Meets ANSI/TIA-568-C.2, ISO/IEC 11801 and IEC 60603-7 standards

#### Built-In Cable-Management Loom in Rear

- Keeps cabling efficiently organized and reduces clutter
- 48 nylon cable ties included

#### Specially Designed for Easy Punchdown Termination

- Simply remove upper level for easy access to lower level of ports

#### Quick, Easy Installation

- Mounts easily into 1U of EIA-standard 19 in. rack

### Highlights

- Heavy-duty 14ga cold-rolled steel construction
- Built-in cable-management loom reduces clutter
- Numbered ports for easy connection identification
- Color-coded for 568A/B wiring
- Mounts into 1U of EIA-standard 19 in. rack

### Package Includes

- N052-048-1U 48-Port 1U Rack-Mount High-Density 110-Type Patch Panel
- (48) Nylon cable ties
- Owner's manual

**TAA-Compliant**

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

## Specifications

| OVERVIEW                            |                            |
|-------------------------------------|----------------------------|
| UPC Code                            | 037332197474               |
| Product Type                        | Punchdown                  |
| Technology                          | Cat5/5e                    |
| PHYSICAL                            |                            |
| Shipping Dimensions (hwd / in.)     | 2.00 x 4.20 x 20.50        |
| Shipping Dimensions (hwd / cm)      | 5.08 x 10.67 x 52.07       |
| Shipping Weight (lbs.)              | 3.70                       |
| Shipping Weight (kg)                | 1.68                       |
| Unit Dimensions (hwd / in.)         | 0.000 x 0.000 x 0.000      |
| CONNECTIONS                         |                            |
| Number of Ports                     | 48                         |
| Side A - Connector 1                | 110 IDC                    |
| Side B - Connector 1                | RJ45 (FEMALE)              |
| STANDARDS & COMPLIANCE              |                            |
| Product Compliance                  | Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT                  |                            |
| Product Warranty Period (Worldwide) | Lifetime limited warranty  |