




SD Cards SDXC/SDHC 300S

Transcend's SDXC/SDHC 300S memory cards provide the performance and capacity necessary to harness the full power of your UHS-I compliant digital camera or camcorder. In addition to incredible transfer speeds, the cards meet UHS Video Speed Class 30 (V30) standards, allowing for smooth, uninterrupted 4K video capture.

V30 compliance applies only to 128GB-512GB capacity cards.



Record your everyday life

Let this moment stay by selecting the right memory card for your camera. Featuring high capacities and excellent performance, Transcend's SDXC/SDHC 300S memory cards are great for recording slices of everyday life.



Show the transfer capabilities

Transcend's SDXC/SDHC 300S memory cards meet both the UHS Speed Class 3 (U3) and the UHS Video Speed Class 30 (V30) standards for 4K Ultra HD video recordings, with read/write speeds of up to 100MB/s and 85MB/s respectively.

U3 and V30 compliance applies only to 128GB-512GB capacity cards.



Store as many as you wish

With up to 512GB storage capacity, Transcend's SDXC/SDHC 300S memory cards allow for thousands of photos and hours of Full HD videos to be recorded, meaning you can stay focused on capturing fantastic moments without worrying about running out of storage.



SD Cards SDXC/SDHC 300S

Features

- Compliant with UHS-I U3 and V30 standards
- Up to 100 MB/s read; 85 MB/s write
- Ideal for digital camera or camcorder
- Built with high-quality 3D NAND flash (2D NAND flash for 16GB and below)



RecoveRx

RecoveRx is a data recovery software for memory cards, USB flash drives, external hard drives and SSDs.

Specifications

Appearance

Dimensions	32 mm x 24 mm x 2.1 mm (1.26" x 0.94" x 0.08")
Weight	2 g (0.07 oz)

Storage

Capacity	4 GB / 8 GB / 16 GB / 32 GB / 64 GB / 128 GB / 256 GB / 512 GB
Flash Type	3D NAND flash 2D NAND flash

Operating Environment

Operating Temperature	-25°C (-13°F) ~ 85°C (185°F)
Operating Voltage	2.7V ~ 3.6V

Performance

Speed Class	UHS-I U3 UHS-I U1 Class 10 V30 V10
Read Speed (Max.)	up to 100 MB/s
Write Speed (Max.)	up to 85 MB/s
Insertion/Removal Cycles	10,000

Warranty

Certificate	CE / FCC / RCM / EAC
Warranty	Five-year Limited Warranty

Compatibility

Supported Device	Interchangeable-lens cameras / Digital cameras / Camcorders
------------------	---

Ordering Information

4GB	TS4GSDC300S
8GB	TS8GSDC300S
16GB	TS16GSDC300S
32GB	TS32GSDC300S
64GB	TS64GSDC300S
128GB	TS128GSDC300S
256GB	TS256GSDC300S
512GB	TS512GSDC300S

Product specifications are subject to change without notice. Pictures shown may differ from actual products. Total accessible capacity varies depending on operating environment.