
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT 2025 TE Connectivity. ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD





NOTE:


1. MATERIAL:
HOUSING: THERMO PLASTIC, UL94-V0, BLACK
CONTACT: COPPER ALLOY
SOLDER BALL: LEAD FREE SOC SOLDERING ALLOY

2. FINISH:
GOLD PLATING ON CONTACT AREA, NICKEL UNDERPLATING OVERALL









THIS PRINT IS

PRELIMINARY

UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

POSITION	PART NO.
560	2534040-5
400	2534040-4
160	2534040-2
80	2534040-1

DIM K	DIM H	DIM G	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	PART NO.
10.25	3.05	8.255	54.38	27.89	16.56	19.76	49.53	55.78	2534040-5
10.25	3.05	5.715	54.38	27.89	11.48	14.68	49.53	55.78	2534040-4
10.25	3.05	5.715	54.38	27.89	11.48	14.68	49.53	55.78	2534040-2
6.00	2.01	1.905	28.98	15.19	3.86	7.06	24.13	30.38	2534040-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.3
3 PLC ±0.2
4 PLC ±-
ANGLES ±-

MATERIAL 1

FINISH 2

DWN NINA LIU 22OCT25
CHK NAVEEN V 22OCT25
APVD SATHISH P 22OCT25
PRODUCT SPEC 108-161995
APPLICATION SPEC 114-161791
WEIGHT -

TE Connectivity

NAME 56G MEZZ 3.5H PLUG ASSY.
-

SIZE A2 | CAGE CODE 00779 | DRAWING NO C-2534040 | RESTRICTED TO -

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 4 | REV 2

PRELIMINARY


1471-9 (3/13)

Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT 2025 TE Connectivity. ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD




2534040-1




2534040-2&2534040-4



2534040-5



SECTION A-A
2534040-4



SECTION A-A
2534040-2

THIS PRINT IS

PRELIMINARY

UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.3
3 PLC ±0.2
4 PLC ±-
ANGLES ±-

MATERIAL

FINISH

DWN	NINA LIU	22OCT25
CHK	NAVEEN V	22OCT25
APVD	SATHISH P	22OCT25
PRODUCT SPEC	108-161995	
APPLICATION SPEC	114-161791	
WEIGHT	-	

TE Connectivity

NAME
56G MEZZ
3.5H PLUG ASSY.
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2534040	-


CUSTOMER DRAWING | SCALE 2:1 | SHEET 2 OF 4 | REV 2


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT 2025 TE Connectivity. ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD





THIS PRINT IS

PRELIMINARY

UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

DIM 5	DIM 4	DIM 3	DIM 2	DIM 1	PART NO.
3.05	8.255	16.51	49.53	54.38	2534040-5
3.05	5.715	11.43	49.53	54.38	2534040-4
2.01	1.905	3.81	24.13	28.98	2534040-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.3
3 PLC ±0.2
4 PLC ±-
ANGLES ±-

MATERIAL 1

FINISH 2

DWN	NINA LIU	22OCT25
CHK	NAVEEN V	22OCT25
APVD	SATHISH P	22OCT25
PRODUCT SPEC	108-161995	
APPLICATION SPEC	114-161791	
WEIGHT	-	

TE Connectivity

NAME 56G MEZZ 3.5H PLUG ASSY. -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2534040	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 3 OF 4 | REV 2


1471-9 (3/13)

Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT 2025 TE Connectivity. ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD



THIS PRINT IS

PRELIMINARY

UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

DIM W	DIM V	DIM U	PART NO.
28	84.4	88	2534040-5
24	84.4	88	2534040-4
24	84.4	88	2534040-2
16	52.4	56	2534040-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.3
3 PLC ±0.2
4 PLC ±-
ANGLES ±-

MATERIAL 1

FINISH 2

DWN NINA LIU 220CT25
CHK NAVEEN V 220CT25
APVD SATHISH P 220CT25
PRODUCT SPEC 108-161995
APPLICATION SPEC 114-161791
WEIGHT -

TE Connectivity

NAME 56G MEZZ 3.5H PLUG ASSY. -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2534040	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 4 OF 4 | REV 2

1471-9 (3/13)

Downloaded from Arrow.com.