4-Port USB 2.0 Ultra-Mini Hub

MODEL NUMBER: **U222-004**



Connect up to four USB devices to a single USB port

Highlights

- Compact design with built-in Cable, perfect for travel
- USB 2.0 480mbps data transfer
- Bus powered through computer connection

Package Includes

- U222-004 4-port USB 2.0 Hub

Description

The U222-004 is an inexpensive way to expand the number of available computer USB ports. Its compact design with built-in cable is perfect for travel, fitting easily into a laptop bag pocket. Supports USB 2.0 data transfer rates up to 480 Mbps and is backward compatible with USB 1.1. Bus powered through the computer's USB port. No external power is required, but the unit includes a USB Micro-B port for an additional connection to the computer in case more power is needed.
All four ports support USB Battery Charging (BC) specification v1.2, providing up to 1.5A for fast charging of mobile devices (BC 1.2 charging requires external power, not included).

Features

- 4-port USB 2.0 Compact Hub
- Built-in cable, 6-in.
- Micro-B port included for additional power from computer
- Supports USB Battery Charging v1.2 with additional external power supply (not included)

Specifications

OVERVIEW	
UPC Code	037332182036
Product Type	Hub
Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No

Downloaded from Arrow.com.

DisplayPort Alt Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 2.0
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(4) USB A (FEMALE)
CHARGING	
Charging Ports	(4) USB-A: 5V 1.5A (7.5W)
Charging Ports Details	Requires AC adapter (not included)
Charging Ports / Amps	(4) 1.5A
PHYSICAL	
Color	Black
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	1.00 x 3.90 x 5.30
Shipping Dimensions (hwd / cm)	2.54 x 9.91 x 13.46
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

Downloaded from Arrow.com.

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.