



**Part Number :** [747641201](#)  
**Product Description :** QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 2.0m Length  
**Series Number :** 74764  
**Status :** Active  
**Product Category :** High-Speed I/O Cable Assemblies



## Documents and Resources

### Drawings

[747641201\\_sd.pdf](#)  
[PK-74764-1201-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                            |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Compliant per 2000/53/EC                                                                                |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                                      |
| REACH SVHC         | Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)                  |
| EU RoHS            | Compliant per EU 2015/863                                                                               |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|                        |                                                                                                                                                     |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                                                                              |
| Category               | High-Speed I/O Cable Assemblies                                                                                                                     |
| Series                 | 74764                                                                                                                                               |
| Description            | QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 2.0m Length                                      |
| Assembly Configuration | Dual Ended Connectors                                                                                                                               |
| Comments               | Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths. |
| Connector to Connector | QSFP+-to-4 SFP+                                                                                                                                     |
| Product Name           | QSFP Plus,QSFP+,SFP Plus,SFP+                                                                                                                       |
| Type                   | Pluggable                                                                                                                                           |
| UPC                    | 884982451551                                                                                                                                        |

### Electrical

|           |           |
|-----------|-----------|
| Data Rate | 10.0 Gbps |
| Impedance | 100Ω      |

### Physical

|                     |                       |
|---------------------|-----------------------|
| Cable Bundling      | None                  |
| Cable Length        | 2.0m                  |
| Circuits (Loaded)   | TWO DIFFERENTIAL PAIR |
| Gender              | Male-Male             |
| Lock to Mating Part | Yes                   |

|                 |           |
|-----------------|-----------|
| Net Weight      | 368.000/g |
| Packaging Type  | Bag       |
| Release Style   | Pull Tab  |
| Single Ended    | No        |
| Wire/Cable Type | Twinax    |
| Wire Size (AWG) | 30        |

---

This document was generated on Apr 20, 2026