

Part Number : [428150042](#)
Product Description : Mini-Fit Sr. Crimp Terminal,
Female, 16-14 AWG, Gold (Au)
Series Number : 42815
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

[428150042_sd.pdf](#)

[PK-42815-001-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications


[PS-42815-001-001.pdf](#)

Tooling Specifications

[ATS-638912000-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	42815
Description	Mini-Fit Sr. Crimp Terminal, Female, 16-14 AWG, Gold (Au)
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	High Current/Low Force; See Product Specification for maximum current rating by circuit size and application.
Product Name	Mini-Fit Sr.
UPC	756054457078

Electrical

Current - Maximum per Contact	50.0A
-------------------------------	-------

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin

Net Weight	1.525/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.33mm max.
Wire Size (AWG)	14, 16
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
10.00mm Pitch Mini-Fit Sr. Single Row Receptacle Housings	<u>42816</u>
Mini-Fit Sr. Dual Row Receptacle Housings	<u>43914</u>

Application Tooling

Global

Description	Part Number
FineAdjust Applicator for Mini-Fit Sr. Male and Female Crimp Terminals, 16-14 AWG	<u>2037022900</u>

This document was generated on Dec 18, 2025