Documents



Home > Browse by Category > Connectors > Harsh Environment Connectors > Sealed Circular Connectors > Mini-Con-X Cable End, 8-pin Mixed 2-#16 & 6-#26, Female, Crimp, Bulk

mini-con-x\_cable\_connector\_black

Videos

# CONXALL®

## Mini-Con-X Cable End, 8-pin Mixed 2-#16 & 6-#26, Female,

W6A80-8SG-522W

Crimp, Bulk Out of stock

Drawings:

< View More From This Family

**Buy Now** 

#### Number of Conductors: 8 Product Line: Mini-Con-X

Configuration

**Specifications** 

- Mounting Type: Cord
- Gender: Female
- Contact Size: 16, 26 AWG
- Termination Style: Crimp Contact Plating: Gold
- Color: Black Locking: Locking

Handle Material: Thermoplastic

Sealed: Sealed

Packaging Type: Bulk

- Insert Material: Thermoplastic
- Backshell Style: Long Winged Coupling Ring: Winged
- · Special Feature: Mixed Contact Size
- Insulation Resistance: 100000 MOhms

### Mechanical

Electrical

 Life Cycle: 300 Cycles Coupling Locking Style: Bayonet

Voltage Rating: 300 Volts

Current Rating: 10, 2.5 Amps

- Mounting Torque: 10 in-lbs
- **Environmental** 
  - Temperature Range: -40?C to +85?C

Shielding: Unshielded

Flame Rating: UL 94V-0

- Salt Spray: Mil-Std 202G method 101E condition B
- Minimum Temperature: -40 C Maxiumum Temperature: 85 C
- Compliance

REACH Compliant: Compliant

RoHS Compliant: Compliant

Moisture Resistance: MIL-STD-202G Method 106G

Brand: Conxall

Thermal Shock: Mil-Std 202G method 107G

- IP Rating: IP67 UV Rating: F1
- IP65: 1 IP66: 1
- IP67:1 IP69K: 1
- Current Interruption: Not for Current Interruption Dimensional
- Material

Outer Diameter: 0.71 in

• Cable Opening: 0.25 in

#### • Body Material: Thermoplastic Contact Material: Copper Alloy

 Insert Material Type: UV Resistant O-Ring Material: Silicone

· Contact Plating Type: Gold

Mates With Accessories

#### Mini-Con-X Panel, 8-pin Mixed 2-#16 & 6-#26,

Male, Crimp, Bulk

## Bulk W7A81-8PG-300

Mini-Con-X Panel, 8-pin

Mixed 2-#16 & 6-#26,

Male, PC Tail (0.187 in),

Mini-Con-X Panel, 8-

pin Mixed 2-#16 & 6-

#26, Male, PC Tail

(0.187 in), Bulk

View Details >

Mini-Con-X Panel, 8-pin

Mixed 2-#16 & 6-#26,

Male, PC Tail (0.187 in),

W7A81-8PG-3ES

Mini-Con-X Panel, 8-

pin Mixed 2-#16 & 6-

W8280-8PG-318

Mini-Con-X Cable-to-

Cable, 8-pin #20, Male,

W8280-8PG-519

Mini-Con-X Cable-to-

Cable, 8-pin #20, Male,

W8A82-8PG-315

Mini-Con-X Cable-to-

Cable, 8-pin Mixed 2-

#16 & 6-#26, Male,

Solder Cup, Bulk

Crimp, Bulk

View Details >

Crimp, Bulk

View Details >

#26, Male, PC Tail

(0.187 in), Bulk

View Details >

Bulk

Mini-Con-X Panel, 8-pin

Mixed 2-#16 & 6-#26,

Male, Solder Cup, Bulk

W7A82-8PG-300

Mini-Con-X Panel, 8-

pin Mixed 2-#16 & 6-

View Details >

Bulk

#26, Male, Solder Cup,

W8280-8PG-321

Mini-Con-X Cable-to-

Cable, 8-pin #20, Male,

W8280-8PG-522

Mini-Con-X Cable-to-

Cable, 8-pin #20, Male,

Crimp, Bulk

View Details >

Crimp, Bulk

View Details >

#26, Male, Crimp, Bulk View Details >

W7A80-8PG-300

Mini-Con-X Panel, 8-

pin Mixed 2-#16 & 6-

W8280-8PG-311

Mini-Con-X Cable-to-

Cable, 8-pin #20, Male,

Crimp, Bulk

View Details >

W8280-8PG-513

Crimp, Bulk

View Details >

Mini-Con-X Cable-to-

Cable, 8-pin #20, Male,

W8280-8PG-528 Mini-Con-X Cable-to-Cable, 8-pin #20, Male, Crimp, Bulk

W8A82-8PG-3DC Mini-Con-X Cable-to-Cable, 8-pin Mixed 2-#16 & 6-#26, Male, Solder Cup, Bulk

View Details >

W8A82-8PG-526 Mini-Con-X Cable-to-

Cable, 8-pin Mixed 2-

View Details >

Solder Cup, Bulk View Details >

#16 & 6-#26, Male,

W8280-8PG-315

Mini-Con-X Cable-to-

Crimp, Bulk

View Details >

Cable, 8-pin #20, Male,

W8280-8PG-516 Mini-Con-X Cable-to-Cable, 8-pin #20, Male,

Crimp, Bulk

View Details >

Cable, 8-pin Mixed 2-#16 & 6-#26, Male, Solder Cup, Bulk

W8A82-8PG-311

Mini-Con-X Cable-to-

W8A82-8PG-513

Mini-Con-X Cable-to-

W8A82-8PG-528

Mini-Con-X Cable-to-

Cable, 8-pin Mixed 2-

#16 & 6-#26, Male,

Solder Cup, Bulk

View Details >

Solder Cup, Bulk

View Details >

View Details >

Cable, 8-pin Mixed 2-#16 & 6-#26, Male,

W8A82-8PG-516 Mini-Con-X Cable-to-Cable, 8-pin Mixed 2-#16 & 6-#26, Male, Solder Cup, Bulk

View Details >

View Details >

W8A82-8PG-318 Mini-Con-X Cable-to-Cable, 8-pin Mixed 2-#16 & 6-#26, Male, Solder Cup, Bulk

View Details >

W8A82-8PG-519

Mini-Con-X Cable-to-

Cable, 8-pin Mixed 2-

#16 & 6-#26, Male,

Solder Cup, Bulk

View Details >

Crimp, Bulk View Details >

W8280-8PG-3DC

Mini-Con-X Cable-to-

Cable, 8-pin #20, Male,

Mini-Con-X Panel, 8-pin

Mixed 2-#16 & 6-#26,

Male, Solder Cup, Bulk

W7A82-8PG-3ES

Mini-Con-X Panel, 8-

pin Mixed 2-#16 & 6-

View Details >

Bulk

#26, Male, Solder Cup,

W8280-8PG-526 Mini-Con-X Cable-to-

Crimp, Bulk

View Details >

Mini-Con-X Cable-to-Cable, 8-pin Mixed 2-#16 & 6-#26, Male, Solder Cup, Bulk

W8A82-8PG-321

Cable, 8-pin #20, Male,

View Details >

W8A82-8PG-522

Mini-Con-X Cable-to-

Cable, 8-pin Mixed 2-

#16 & 6-#26, Male,

Solder Cup, Bulk

View Details >



Privacy | Contact Us | Login

Downloaded from Arrow.com

Switchcraft: 773-792-2700 Conxall: 630-834-7504











© 2024 Switchcraft and Conxall. All Rights Reserved.