


216005-1 Product Details

Share

Print

Email



216005-1

TE Internal Number: 216005-1

Active

View 3D PDF

Cable Mounted Jacks

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector - Modular
- Region = Not Specified
- Jack Type = RJ45
- Not Shielded
- Housing Color = Black

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Toolless Modular Jack kit, 8 pos., for discrete wires \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [side entry, bottom entry, top entry and toolless mod... \(PDF, English\)](#)

Application Specifications:

- [application specification for toolless modular jack \(PDF, English\)](#)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version P\)](#)
- [3D Model \(IGES, Version P\)](#)
- [3D Model \(STEP, Version P\)](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector - Modular
- Jack Type = RJ45
- Termination Style = Toolless
- Series = DEC Connect
- [Wiring Pattern](#) = One-to-one
- [Keyed](#) = No
- Latch Style = Standard
- Stuffer Cap Material = A.B.S.

Electrical Characteristics:

- Shielded = No

Body Features:

- NETCONNECT Select System = No
- Mount Type = Panel Mount

Contact Features:

- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Gold Flash over Palladium Nickel

Housing Features:

- Housing Color = Black
- Housing Material = PBT - GF
- UL Flammability Rating = UL 94-HB

Configuration Features:

- Number of Positions = 8

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:

- Packaging Method = Bulk
- Packaging Quantity = Bulk

Product Availability:

- Region = Not Specified

Other:

- Brand = AMP

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

