molex



**Part Number :** 936014219
**Product Description :** Heavy-Duty Standard (STD) Cover, Die-cast Aluminum, with 4 Pegs, with Gasket, Size 32A «66x40», Grey
**Series Number :** 93601
**Status :** Active
**Product Category :** Heavy-Duty Connectors
**Engineering Part Number :** 7832.4673.0

## Documents and Resources

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Contained per ED/71/2019 (16 July 2019) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Heavy Duty Connectors |
| Series | 93601 |
| Description | Heavy-Duty Standard (STD) Cover, Die-cast Aluminum, with 4 Pegs, with Gasket, Size 32A «66x40», Grey |
| Comments | With nylon wire tether line. |
| Component Type | Cover |
| IP Rating | IP66 |
| Product Name | Heavy-Duty Connectors |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type | STD |
| UPC | 887191888354 |

### Agency

| | |
|---|---|
| CSA | 256883 |
| UL | E249674 |

### Electrical

| | |
|---|---|
| Voltage - Maximum | 500V |

### Physical

| | |
|---|---|
| Component Size | 32A «66x40» |
| Cover Coating | Polyester Powder |
| Cover Color | Grey RAL 7037 |
| Lock to Mating Part | Yes |
| Material - Cover | Die-cast Aluminum |
| Material - Gasket | NBR |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Peg | Stainless Steel |
| Net Weight | 69.000/g |
| Number of Pegs | 4 |
| Packaging Type | Bag |
| Thread Size | N/A |
| Thread Type | N/A |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number |
|---|---|
| Use With | Size 32A «66x40» Housings with 2 Levers |



Downloaded from Arrow.com.