**Part Number :** 1300980025
**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip, 1/4" NPT, Straight Male, Cable Diameter 3.43-5.08mm (.135-.200")
**Series Number :** 130098
**Status :** Active
**Product Category :** Cable Grips
**Engineering Part Number :** 5400




## Documents and Resources

### Drawings

1300980025_sd.pdf

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2020)9139-DC (19 Jan 2021) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Cable Grips |
| Series | 130098 |
| Description | MAX-LOC Strain Relief Cord-Sealing Grip, 1/4" NPT, Straight Male, Cable Diameter 3.43-5.08mm (.135-.200") |
| NEMA Rating | NEMA 3R |
| Product Name | MAX-LOC |
| Type | Strain Relief Grip |
| UPC | 78678854000 |

### Agency

| | |
|---|---|
| CSA | LR32159 |

### Physical

| | |
|---|---|
| Approximate Break Strength | N/A |
| Bale Length | N/A |
| Body Style | Straight |
| Cable Diameter | 3.43-5.08mm (.135-.200") |
| Color - Grommet | Gray |
| Eye Type | N/A |
| Gender | Male |
| Material - Body | Nylon |
| Material - Grip | N/A |
| Mesh Length | N/A |
| Net Weight | 133.330/g |
| Number of Holes | 1 |
| O-Ring | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Thread Size | 1/4" NPT |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number |
|---|---|
| MAX-LOC Lock Nut 1/4" NPT | 1300990141 |
| MAX-LOC Gasket Sealing Ring, 1/4" NPT, Black | 1300990147 |



Downloaded from Arrow.com.