

Cable lug - C-BCI 6/2,8 - 3240047

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flat pin cable lug, with tab, soldered neck, yellow, 4 ... 6 mm², pin width: 2.8 mm, easy conductor entry with Easy-Entry, for horizontal and vertical crimping with CRIMPFOX-RCI 6

Your advantages

- ✓ 'EASY ENTRY' for easy and reliable conductor entry
- ✓ Halogen-free
- ✓ Electrolytic tin plating

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 452656
GTIN	4046356452656
Weight per Piece (excluding packing)	1.600 g
Custom tariff number	85369010
Country of origin	Taiwan

Technical data

Dimensions

Length (b)	32 mm
Width (a)	2.8 mm
Maximum stripping length	9 mm
Length contact range	18 mm
Length of insulation sleeve (c)	14 mm

Cable lug - C-BCI 6/2,8 - 3240047

Technical data

Dimensions

Inner dimension of the insulating collar (d)	6.5 mm
Material thickness (g)	0.8 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
Short-term temperature	120 °C
Max. permanent temperature	105 °C

General


Color	yellow
Stripping length	9 mm
Components	halogen-free
Material	Copper
Flammability rating according to UL 94	V2
Insulating material	PA
Coating	tin-plated

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27400204
eCl@ss 11.0	27400204
eCl@ss 4.0	27060700
eCl@ss 4.1	27060700

Cable lug - C-BCI 6/2,8 - 3240047

Classifications

eCl@ss

eCl@ss 5.0	27400200
eCl@ss 5.1	27400200
eCl@ss 6.0	27400200
eCl@ss 7.0	27400204
eCl@ss 9.0	27400204

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 6.0	EC001052
ETIM 7.0	EC001052

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121707
UNSPSC 18.0	27121707
UNSPSC 19.0	27121707
UNSPSC 20.0	27121707
UNSPSC 21.0	27121707

Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-RCI 6 - 1212057



Crimping pliers, for insulated cable lugs, 0.5 mm² ... 6.0 mm² (red, blue, yellow), oval crimp, symmetrical

Cable lug - C-BCI 6/2,8 - 3240047

Accessories

Crimping pliers - CRIMPFOX-RCI 2,5 - 1212053



Crimping pliers, for insulated cable lugs, 0.5 mm² ... 2.5 mm² (red, blue), oval crimp

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>