


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0010021057
Status: Planned for Obsolescence
Description: 5.08mm (.200") Pitch SPOX™ Header, Vertical, 5 Circuits

Documents:

- [3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-2767-004 \(PDF\)](#)
[Product Specification PS-2767-012 \(PDF\)](#)
[Product Specification PS-2767-013 \(PDF\)](#)
[Product Specification PS-5197-003 \(PDF\)](#)
- [Product Specification PS-5197-004 \(PDF\)](#)
[Product Specification PS-5279-001 \(PDF\)](#)
[Product Specification PS-5279-002 \(PDF\)](#)
[Packaging Specification SPK-5279-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)



Agency Certification

CSA	LR19980
TUV	R72090224
UL	E29179

General

Product Family	PCB Headers
Series	5279
Application	Power, Wire-to-Board
Product Name	SPOX™

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Plating Mating	Tin
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.60mm (.142")
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	5.08mm (.200")
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	7A
Voltage - Maximum	250V

Material Info

Old Part Number	5279-05A
-----------------	----------

Reference - Drawing Numbers

EU RoHS **China RoHS**

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
5279Series

Mates With
5197 SPOX™ Crimp Housing

Packaging Specification
Product Specification

Sales Drawing

SPK-5279-001
PS-2767-004, PS-2767-012, PS-2767-013,
PS-5197-003, PS-5197-004, PS-5279-001,
PS-5279-002, RPS-5279-012
SD-5279-NA

This document was generated on 05/23/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION