







REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	20SEP2016	DW	CW
	B	ECR-20-016312	03JUN2021	BS	CW

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释
1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)

T1910102140-009	H10BPR-TSH-M40-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M40, POWDER COATED,GREY H10BPR对角锁定侧出上壳M40 灰色	M40	
T1910102132-009	H10BPR-TSH-M32-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M32, POWDER COATED,GREY H10BPR对角锁定侧出上壳M32 灰色	M32	
T1910102129-009	H10BPR-TSH-PG29-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG29, POWDER COATED,GREY H10BPR对角锁定侧出上壳PG29 灰色	PG29	
T1910102125-009	H10BPR-TSH-M25-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M25, POWDER COATED,GREY H10BPR对角锁定侧出上壳M25 灰色	M25	
T1910102121-009	H10BPR-TSH-PG21-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG21, POWDER COATED,GREY H10BPR对角锁定侧出上壳PG21 灰色	PG21	
T1910102120-009	H10BPR-TSH-M20-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M20, POWDER COATED,GREY H10BPR对角锁定侧出上壳M20 灰色	M20	
T1910102116-009	H10BPR-TSH-PG16-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG16, POWDER COATED,GREY H10BPR对角锁定侧出上壳PG16 灰色	PG16	
T1910101140-009	H10BPR-TSH-M40-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M40, POWDER COATED,SILVER WHITE H10BPR对角锁定侧出上壳M40 银白色	M40	
T1910101132-009	H10BPR-TSH-M32-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M32, POWDER COATED,SILVER WHITE H10BPR对角锁定侧出上壳M32 银白色	M32	
T1910101129-009	H10BPR-TSH-PG29-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG29, POWDER COATED,SILVER WHITE H10BPR对角锁定侧出上壳PG29 银白色	PG29	
T1910101125-009	H10BPR-TSH-M25-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M25, POWDER COATED,SILVER WHITE H10BPR对角锁定侧出上壳M25 银白色	M25	
T1910101121-009	H10BPR-TSH-PG21-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG21, POWDER COATED,SILVER WHITE H10BPR对角锁定侧出上壳PG21 银白色	PG21	
T1910101120-009	H10BPR-TSH-M20-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M20, POWDER COATED,SILVER WHITE H10BPR对角锁定侧出上壳M20 银白色	M20	
T1910101116-009	H10BPR-TSH-PG16-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG16, POWDER COATED,SILVER WHITE H10BPR对角锁定侧出上壳PG16 银白色	PG16	
T1910100140-009	H10BPR-TSH-M40-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M40, POWDER COATED,BLACK H10BPR对角锁定侧出上壳M40 黑色	M40	
T1910100132-009	H10BPR-TSH-M32-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M32, POWDER COATED,BLACK H10BPR对角锁定侧出上壳M32 黑色	M32	
T1910100129-009	H10BPR-TSH-PG29-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG29, POWDER COATED,BLACK H10BPR对角锁定侧出上壳PG29 黑色	PG29	
T1910100125-009	H10BPR-TSH-M25-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M25, POWDER COATED,BLACK H10BPR对角锁定侧出上壳M25 黑色	M25	
T1910100121-009	H10BPR-TSH-PG21-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG21, POWDER COATED,BLACK H10BPR对角锁定侧出上壳PG21 黑色	PG21	
T1910100120-009	H10BPR-TSH-M20-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY M20, POWDER COATED,BLACK H10BPR对角锁定侧出上壳M20 黑色	M20	
T1910100116-009	H10BPR-TSH-PG16-EMC-C	H10BPR HOOD, DIAGONAL LOCKING, SIDE ENTRY PG16, POWDER COATED,BLACK H10BPR对角锁定侧出上壳PG16 黑色	PG16	
PART NUMBER 料号	PART DESCRIPTION 描述			PG/M THREAD PG/M 螺纹

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		DWN DAVID WANG 20SEP2016 CHK CHRIS WANG 20SEP2016 APVD XIANG XU 20SEP2016 PRODUCT SPEC 108-137191 APPLICATION SPEC 114-137191 WEIGHT CUSTOMER DRAWING	NAME H10BPR-TSH-PG/M-EMC-C SIZE A1 CASE CODE - DRAWING NO. ©=T19101010XXXXX09 RESTRICTED TO	SCALE 1:1 SHEET 1 OF 1 REV B
---	--	---	---	------------------------------------