**Part Number :** 340624003
**Product Description :** MX150 Cable-Sealed Female Connector Assembly, Single Row, 2 Circuits, Severe Vibration Housing with Keying Option C, Black
**Series Number :** 34062
**Status :** Active
**Product Category :** Connector Housings



## Documents and Resources

### Drawings

340624003_sd.pdf

PK-30907-879-001.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

340620000-AS-CH-000.pdf

AS-34062-000-001.pdf

PS-34062-000-001.pdf

TS-34062-992-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant |
| China RoHS | Not Relevant |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026) |

Downloaded from Arrow.com.

| | |
|---|---|
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 34062 |
| Description | MX150 Cable-Sealed Female Connector Assembly, Single Row, 2 Circuits, Severe Vibration Housing with Keying Option C, Black |
| Application | Power, Wire-to-Wire, Automotive |
| Comments | No Connector Position Assurance (CPA) |
| Product Name | MX150 |
| UPC | 887191462332 |

### Physical

| | |
|---|---|
| Circuits (maximum) | 2 |
| Color - Resin | Black |
| Gender | Receptacle |
| Glow-Wire Capable | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 4.630/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 5.00mm |
| Pitch - Termination Interface | 5.00mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +155°C |

### Solder Process Data

| | |
|---|---|
| Lead-Free Process Capability | N/A |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| MX150 Cable-Sealed Male Connector Assemblies | 34675 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| MX150 Cable Seal Female Terminals | 34083 |
| MX150 Cable Seal Female Terminals | 34081 |



Downloaded from Arrow.com.