

<https://www.wago.com/711-155>



Similar to illustration

Die Transformatorenklemmen haben die Artikelnummer 711-155 und ermöglichen einen einfachen und sicheren Anschluss. Bei diesen Transformatorenklemmen ist für den Leiteranschluss eine Abisolierlänge im Bereich von 9 bis 10 mm erforderlich. Dieses Produkt ist mit der CAGE CLAMP®-Technologie ausgerüstet. Mit dem CAGE CLAMP® Universalanschluss steht Ihnen eine zuverlässige und wartungsfreie Anschluss-technik zur Verfügung, um sämtliche Leiterarten mithilfe einer Käfigzugfeder anzuschließen. Es ist keine Vorbehandlung der Leiter notwendig, beispielsweise durch das Aufcrimpen von Aderendhülsen. In Breite x Höhe x Tiefe sind die Abmessungen (37,5 x 35 x 23,5) mm.

Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	800 V	-
Rated surge voltage	-	8 kV	-
Rated current	-	25 A	-

Clamping units	5
Total number of potentials	5
Number of connection types	1

Connection 1	
Connection technology	CAGE CLAMP®
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches
Pole number	5

Width	37.5 mm / 1.476 inches
Height	35 mm / 1.378 inches
Depth	23.5 mm / 0.925 inches



Material data		
Note (material data)		Information on material specifications can be found here
Color		gray
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.356 MJ
Weight		17.2 g

Commercial data		
PU (SPU)		30 pcs
Packaging type		Box
Country of origin		DE
GTIN		4044918819589
Customs tariff number		85369010000

Product classification		
UNSPSC		39121410
eCl@ss 10.0		27-14-11-10
eCl@ss 9.0		27-14-11-10
ETIM 9.0		EC000398
ETIM 8.0		EC000398
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60998	NTR NL-7194
CCA DEKRA Certification B.V.	EN 60998	2160584.54
CSA DEKRA Certification B.V.	C22.2 No. 158	1101145
UL UL International Germany GmbH	UL 1059	E45172

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-



Downloads			
Environmental Product Compliance			
Compliance Search			
Environmental Product Compliance 711-155			

Documentation			
Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	

CAD/CAE-Data			
CAD data		CAE data	
2D/3D Models 711-155		EPLAN Data Portal 711-155	
		WSCAD Universe 711-155	
		ZUKEN Portal 711-155	