



**Part Number :** [1300970247](#)  
**Product Description :** Deluxe Cord Grips Strain Relief, 2" NPT, Straight Male, Cable Diameter 42.67-45.97mm (1.680-1.810")  
**Series Number :** 130097  
**Status :** Active  
**Product Category :** Cable Grips  
**Engineering Number :** 36487



Documents & Resources

Drawings  
[1300970247 sd.pdf](#)

Product Environment Compliance

Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

## Part Details

### General

|                     |                                                                                                     |
|---------------------|-----------------------------------------------------------------------------------------------------|
| Status              | Active                                                                                              |
| Category            | Cable Grips                                                                                         |
| Series              | 130097                                                                                              |
| Description         | Deluxe Cord Grips Strain Relief, 2" NPT, Straight Male, Cable Diameter 42.67-45.97mm (1.680-1.810") |
| Hazardous Locations | Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2                                    |
| NEMA Rating         | NEMA 4                                                                                              |
| Product Name        | Deluxe Cord                                                                                         |
| Type                | Strain Relief Grip                                                                                  |
| UPC                 | 78678836487                                                                                         |

### Agency

|     |         |
|-----|---------|
| CSA | LR32159 |
|-----|---------|

### Physical

|                            |                              |
|----------------------------|------------------------------|
| Approximate Break Strength | N/A                          |
| Bale Length                | N/A                          |
| Body Style                 | Straight                     |
| Cable Diameter             | 42.67-45.97mm (1.680-1.810") |
| Color - Grommet            | N/A                          |
| Eye Type                   | N/A                          |
| Gender                     | Male                         |
| Material - Body            | Aluminum                     |
| Material - Grip            | Stainless Steel              |
| Mesh Length                | N/A                          |
| Number of Holes            | N/A                          |
| O-Ring                     | N/A                          |
| Thread Size                | 2" NPT                       |