




166632-1 Product Details

Share Print Email



166632-1

TE Internal Number: 166632-1

Active

Eurocard Contacts

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Eurocard Product Line
- Contact Type = Socket
- Contact Angle = Straight
- Applies To Cable
- Wire Range = 0.12-0.60² [26-20] mm [AWG]

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [crimp-on/snap-in tab receptacle strir \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = Eurocard
- Wire Insulation Diameter (mm [in]) = 1.10 - 1.80 [0.043 - 0.071]
- Make First / Break Last = No
- DIN Level = I
- Used For = Type F Vertical Housing
- Termination Method to Wire/Cable = Crimp

Mechanical Attachment:

- Contact Retention in Housing = Crimp Snap-In

Body Features:

- Wire Range (mm [AWG]) = 0.12-0.60² [26-20]

Contact Features:

- Contact Type = Socket
- Contact Angle = Straight
- Contact Configuration = Snap-In
- Contact Base Material = Phosphor Bronze

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- Applies To = Cable

Packaging Features:

- Packaging Method = Loose Piece

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

