




1734085-1 Product Details

Share

Print

Email



Active

View 3D PDF

Universal Serial Bus (USB) Connectors

USB Conn., A series, V/T, PBT.DIP

1734085-1

TE Internal Number: 1734085-1

Product Highlights [View All](#)

- USB 2.0 Industry Standard
- Size = Standard
- A Series
- Receptacle
- Without Locking Feature

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Size	Standard
Gender	Receptacle
Orientation	Vertical
LED	Without
PCB Mount Retention Type	Kinked Leg(s)

Mechanical Attachment

Mount Location	Top
----------------	-----

Termination Features

Contact Termination Type	Through Hole
Termination Method	Solder

Dimensions

PCB Thickness, Recommended (mm [in])	1.60 [0.063]
Tail Length (mm [in])	2.8 [0.11]

Body Features

Locking Feature	Without
Panel Ground	Without
Shell Plating	Nickel over Copper
Assembly Process Feature	Without Pick and Place Cover
Locating Post(s)	Without

Contact Features

Contact Plating, Mating Area, Material	Gold
Contact Plating, Mating Area, Thickness (µm [µin])	0.76 [29.92]

Housing Features

Housing Color	Black
Housing Material	PBT GF

Configuration Features

Number of Ports	1
Number of Positions	4

Industry Standards

Industry Standard	USB 2.0
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Wave solder capable to 240°C
RoHS/ELV Compliance History	Always was RoHS compliant
USB-IF Test ID Number (TID)	61000806

Conditions for Usage

Applies To	Printed Circuit Board
------------	-----------------------

Packaging Features

Packaging Method	Tray/Box
------------------	----------

Other

Series	A
Brand	AMP
Node Classification	USB Connectors

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

