

Part Number : [988161111](#)

Product Description : NSCC Unsealed Female Housing, 10 Circuits, Dual Row, Black, Version 1 without Ear

Series Number : 98816

Status : Not Recommended For New Design

Product Category : Connector Housings

Engineering Part Number : 18101EV10M1



Documents and Resources

Drawings

[988161111_sd.pdf](#)

Specifications

[AS-98816-001-001.pdf](#)

[PK-98816-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	98816
Description	NSCC Unsealed Female Housing, 10 Circuits, Dual Row, Black, Version 1 without Ear
Application	Wire-to-Wire
Comments	Pitch Center Spacing: Horizontal Pitch 3.33mm, Vertical pitch 6.00mm
Component Type	Receptacle
Product Name	NSCC
UPC	822348816293

Physical

Circuits Detail	10x1.5mm female terminals
Circuits (maximum)	10
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	4.700/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.33mm, 6.00mm

Polarized to Mating Part	Yes
Ports	1
Sealed	Unsealed
Temperature Range - Operating	-40° to +85°C
Terminal Size	1.5

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
NSCC Male Housing, Terminal Size 1.50mm, Non-Sealed, 5.0mm Pitch, 10 Circuits, Black	<u>988231011</u>

Use with Part(s)

Description	Part Number
NSCC Receptacle Terminals Size 1.5	<u>98897</u>

Application Tooling

Global

Description	Part Number
Extractor Tool for NSCC Female Housing	<u>638137500</u>

This document was generated on Sep 10, 2026