
molex



Part Number : 2030705242
Product Description : Mini-Fit TPA2/Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 20-18 AWG, 2.10-2.85mm Insulation Diameter, Loose
Series Number : 203070
Status : Active
Product Category : Crimp Terminals

Documents and Resources

Drawings

2030705242_sd.pdf

2030700003-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-172718-0000-001.pdf

2131370000-AS-000.pdf

2029880001-PS-000.pdf

1727180003-TS-000.pdf

2029880001-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:a58ab0b4-d5f3-47ff-b9a7-26e8d01d8262
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	203070
Description	Mini-Fit TPA2/Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 20-18 AWG, 2.10-2.85mm Insulation Diameter, Loose
Application	Power
Comments	See product specification for current derating information.
Product Name	Mini-Fit Sigma,Mini-Fit TPA2
UPC	191128371155

Electrical

Current - Maximum per Contact	13.5A
Voltage - Maximum	600V AC/DC

Physical

Durability (mating cycles max)	30
Gender	Male

Downloaded from Arrow.com.

Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.186/g
Packaging Type	Reel
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.07-1.65mm
Wire Size (AWG)	22, 24
Wire Size mm^2	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Plug Housings	172762
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Plug Housings	172767
Mini-Fit Sigma Sealed Dual Row Plug Housings	207017

Downloaded from Arrow.com.