

Honeywell

THE POWER OF **CONNECTED**

70/75 Series Mobile Computer

Accessories Guide



Contents

- 2 [Docks and Modules](#)
- 5 [Data Cables](#)
- 6 [Handles and Holsters](#)
- 8 [Power Supplies](#)
- 9 [Replacement Parts](#)
- 10 [Mass Storage](#)
- 11 [FlexDock](#)

Docks and Modules

PRODUCT NAME	SKU	DESCRIPTION
Vehicle Dock, CN70/CN70e/ CN75/CN75e 	871-034-001 (1000AV01)	Retains mobile computer in vehicle environment. Easy one-handed removal of device. Provides USB Host (HDB15M) and RS-232 (DB9M) receptacles. Provides 5V DC on RS-232 Pin 9 for powering peripherals. Requires 805-638-001 Mounting Kit and power option listed below. Optional 850-828-001 Audio Adapter via USB port. Optional USB Host Cable VE011-2016. Not compatible with Scan Handle, Magnetic Stripe Reader, or Snap-On Adapters.
Vehicle Holder, CN70/CN70e/ CN75/CN75e 	805-672-001 (1000AV02)	Retains mobile computer in vehicle environment. Does not provide connectivity. Requires 805-638-001 Mounting Kit. Not compatible with Scan Handle, Magnetic Stripe Reader, or Snap-On Adapters.
Vehicle Dock, CK70/CK71/CK75 	871-035-001 (1001AV01)	Retains mobile computer in vehicle environment. Easy one-handed removal of device. Provides USB Host (HDB15M) and RS-232 (DB9M) receptacles. Provides 5V DC on RS-232 Pin 9 for powering peripherals. Requires 805-638-001 Mounting Kit and power option listed below. Optional 850-828-001 Audio Adapter via USB port. Optional USB Host Cable VE011-2016. Compatible with Scan Handle or Magnetic Stripe Reader. Not compatible with Snap-On Adapters.
Vehicle Holder, CK70/CK71/CK75 	805-673-001 (1001AV02)	Retains mobile computer in vehicle environment. Does not provide connectivity. Requires 805-638-001 Mounting Kit. Compatible with Scan Handle or Magnetic Stripe Reader. Not compatible with Snap-On Adapters.

PRODUCT NAME	SKU	DESCRIPTION
Vehicle Dock Mounting Kit 	805-638-001	Required for Vehicle Dock or Vehicle Holder. Consists of one 120.7 mm (4.75 in) adjustable pivot arm with two 38.1 mm (1.5 in) stainless steel balls and assembly hardware. Requires customer-supplied hardware to secure mount to vehicle.
Power Cable, Dock-to-Fuse Block	226-109-003	Power Option: For connection of Vehicle Dock to fuse block or similar connection point. Power Cable with spade lugs. Supports input voltage of 12–30V DC. Optionally used with 203-803-001 Fuse Block Power Kit if direct connection to fuse block not available.
Vehicle Dock Fuse Block Power Kit	203-803-001	Power Distribution Block optionally used 226-109-003 when direct connection to vehicle fuse block is not available.
Vehicle Dock Installation Kit	203-802-001	Power Option: For connection of Vehicle Dock directly to vehicle battery. Includes power cables and cable mounting hardware. Alternate to 70/75 Series Vehicle Dock Power Cable. Supports input voltage of 12–30V DC.
DC/DC Converter Kit, 6–60V DC	203-808-001	Power Option: For connection of Vehicle Dock to forklift power systems operating on 6–60V DC. Provides filtering and conditioning. Includes all power cables and cable mounting hardware.
DC/DC Converter Kit, 15–96V DC	203-809-001	Power Option: For connection of Vehicle Dock to forklift power systems operating on 15–96V DC. Provides filtering and conditioning. Includes all power cables and cable mounting hardware.
Auto Adapter Vehicle Dock 	852-057-005 (1000AA08)	Power Option: For connection of Vehicle Dock screw-down power receptacle to vehicle cigarette lighter/power port.
Audio Adapter, 70/75 Series Vehicle Dock 	850-828-001	Adapts Vehicle Dock USB connector to amplified audio output. Terminates in 3.5 mm Audio Jack. Customer must supply loudspeaker appropriate to application.

PRODUCT NAME	SKU	DESCRIPTION
Snap-On Adapter, Ethernet, 70/75 Series 	850-565-001 (1000AA01)	Provides RJ45 receptacle for Ethernet connectivity via standard cables (not included). Uses optional 851-094-011 AC Power Supply and/or 852-071-001 Vehicle Power Adapter. Charges mobile computer battery in 4 hours or less (typical); up to 6 hours for fully discharged batteries.
Snap-On Adapter, RS-232, 70/75 Series 	850-566-001 (1000AA03)	Provides DB9M receptacle for RS-232 serial communications. Provides 5V DC on Pin 9 for powering peripherals. Uses optional 851-094-011 AC Power Supply and/or 852-071-001 Vehicle Power Adapter. This adapter is NOT compatible with SR61TXR. Charges mobile computer battery in 4 hours or less (typical); up to 6 hours for fully discharged batteries.
Snap-On Adapter, USB, 70/75 Series 	850-567-001 (1000AA07)	Provides HDB15M receptacle for USB Host and Client connectivity. Requires USB cable VE011-2016 (Host) and/or VE011-2018 (Client). Uses optional 851-094-011 AC Power Supply and/or 852-071-001 Vehicle Power Adapter. Charges mobile computer battery in 4 hours or less (typical); up to 6 hours for fully discharged batteries.
Snap-On Adapter, DEX, 70/75 Series 	850-568-001 (1000AA04)	Provides connectivity to DSD receiving systems supporting DEX standards. Terminates in 6.35 mm (0.25 in) DEX plug. Uses optional 851-094-011 AC Power Supply and/or 852-071-001 Vehicle Power Adapter. Charges mobile computer battery in 4 hours or less (typical); up to 6 hours for fully discharged batteries.
Snap-On Adapter, Audio, 70/75 Series 	850-577-001 (1000AA02)	Provides Quick Disconnect (QD) headset connector for use in audio and voice applications. Uses optional 851-094-011 AC Power Supply and/or 852-071-001 Vehicle Power Adapter. Charges mobile computer battery in 4 hours or less (typical); up to 6 hours for fully discharged batteries.

PRODUCT NAME	SKU	DESCRIPTION
Magnetic Stripe Reader (MSR), CN70/CN70e/CN75/CN75e 	850-570-001 (1001AA01)	Reads credit cards and similar cards with data encoded on magnetic stripe. Attaches to docking connector on CN70/CN70e/CN75/CN75e mobile computer. MSR does not need to be removed for docking in FlexDock.
Magnetic Stripe Reader (MSR), CK70/CK71/CK75 	850-574-001 (1000AA06)	Reads credit cards and similar cards with data encoded on magnetic stripe. Attaches to back of mobile computer via Back Accessory Interface (order separately). Not compatible with Scan Handle. Includes shortened handstrap.
Back Accessory Interface, CK70/CK71/CK75 	715-605-001	Replaces back access door on CK70/CK71/CK75 mobile computer. Provides power and data connections to back-mounted peripherals designed for use with CK70/CK71/CK75 mobile computer. Partner Development Guide is available to aid in creating compatible peripheral devices.

Data Cables


PRODUCT NAME	SKU	DESCRIPTION
Cable, Single USB Host 	VE011-2016	Adapts Vehicle Dock USB Connector or USB Snap-On Adapter to USB-A Female receptacle for connectivity to USB Host peripherals. Use optional Cable Retainer Kit (203-810-001, sold separately) to secure USB connectors.
Cable, Single USB Client 	VE011-2018	For use with USB Snap-On Adapter to provide USB Client (ActiveSync) connection to host PC. Use optional Cable Retainer Kit (203-810-001, sold separately) to secure USB connectors.
Kit, USB Cable Retainer (5/pk) 	203-810-001	Contains five (5) sets of Cable Retainers used to secure USB connectors.

Handles and Holsters

PRODUCT NAME	SKU	DESCRIPTION
Scan Handle, CN70/CN70e/ CN75/CN75e 	805-835-001	Snaps easily on or off mobile computer. Angles mobile computer to enable screen viewing while scanning. Optional bracket included for semi-permanent attachment. Not compatible with Vehicle Dock or Holder.
Scan Handle, CK70 	805-836-002	Attaches to mobile computer with screw-in handle. Does not interfere with Vehicle Dock or Holder use. Not compatible with Magnetic Stripe Reader. Slightly obscures the lower portion of the camera field of view.
Scan Handle, CK71/CK75 	805-836-001	Attaches to mobile computer with screw-in handle. Does not interfere with Vehicle Dock or Holder use. Not compatible with Magnetic Stripe Reader.
Holster, CN70/CN75 without Scan Handle 	815-067-001	Holster for CN70 and CN75 mobile computers without Scan Handle.
Holster, CN70/CN70e/CN75/ CN75e with Scan Handle 	815-074-001	Holster for CN70, CN70e, CN75, and CN75e mobile computers with Scan Handle.

PRODUCT NAME	SKU	DESCRIPTION
Holster, CN70e/CN75e without Scan Handle 	815-080-001	Holster for CN70e and CN75e mobile computers without Scan Handle.
Holster, CK71/CK75 without Scan Handle 	815-068-001	Holster for CK71 and CK75 mobile computers without Scan Handle.
Holster, CK71/CK75 with Scan Handle 	815-075-001	Holster for CK71 and CK75 mobile computers with Scan Handle.
Desk Stand, CN70/CN70e/ CN75/CN75e 	203-933-001	Positions mobile computer upright on flat surface; allows connection of adapters and cables.
Desk Stand, CK70/CK71/CK75 	203-934-001	Positions mobile computer upright on flat surface; allows connection of adapters and cables.
Protective Boot, CK71/CK75 	203-961-001	Rubber boot for CK71 and CK75 mobile computers only. Charcoal color. Use with or without handle. (Not compatible with holster or vehicle docks.)


Power Supplies

PRODUCT NAME	SKU	DESCRIPTION
AC Power Supply, 3-Pin Connector 	851-094-011 (9001AE01)	Provides 3-pin quarter-turn locking connector for use with 70/75 Series Snap-On Adapters. Requires AC line cord.
Vehicle Power Adapter, 3-Pin Connector 	852-071-001 (9002AX01)	Provides 3-pin quarter-turn locking connector for power connection between vehicle cigarette lighter/power port and Snap-On Adapters.
Vehicle Power Adapter 	852-074-001	Provides direct power connection between the vehicle cigarette lighter/power port and the 70/75 Series docking connector.
AC Power Cord	321-470-001 321-500-001 071918 1-974027-025 1-974028-025 1-974029-020 1-974030-025 321-471-002 321-501-002 321-502-002	AC Power Cord, Switzerland AC Power Cord, Japan AC Power Cord, China RoHS AC Power Cord, Europe RoHS AC Power Cord, US RoHS AC Power Cord, UK RoHS AC Power Cord, Australia RoHS AC Power Cord, Italy RoHS AC Power Cord, Denmark RoHS AC Power Cord, India/South Africa RoHS
Battery Pack, CN70/CN70e/ CN75/CN75e 	318-043-033	Spare or replacement battery pack for CN70/CN70e/CN75/CN75e mobile computer (one pack included with each mobile computer).

PRODUCT NAME	SKU	DESCRIPTION
Battery Pack, CK70/CK71/CK75 	318-046-031	Spare or replacement battery pack for CK70/CK71/CK75 mobile computer (one pack included with each mobile computer).
Battery Pack, CK75 Cold Storage 	318-046-032	Spare or replacement battery pack for CK75 Cold Storage mobile computer (one pack included with each Cold Storage mobile computer).

Replacement Parts

PRODUCT NAME	SKU	DESCRIPTION
Kit, Tethered Stylus, CN70/ CN70e/CN75/CN75e (5/pk) 	203-932-001	Kit of five (5) replacement styluses for CN70/CN70e/CN75/CN75e mobile computer (one stylus included with each mobile computer).
Kit, Tethered Stylus, CK70/ CK71/CK75 (5/pk) 	203-928-001	Kit of five (5) replacement styluses for CK70/CK71/CK75 mobile computer (one stylus included with each mobile computer).
Kit, Handstrap, CN70/CN75 (5/pk) 	203-930-001	Kit of five (5) replacement handstraps for CN70 and CN75 mobile computer (one handstrap included with each mobile computer).
Kit, Handstrap, CN70e/CN75e (5/pk) 	203-931-001	Kit of five (5) replacement handstraps for CN70e and CN75e mobile computer (one handstrap included with each mobile computer).

PRODUCT NAME	SKU	DESCRIPTION
Kit, Handstrap, CK70/CK71/ CK75 (5/pk) 	203-929-001	Kit of five (5) replacement handstraps for CK70/CK71/CK75 mobile computer (one handstrap included with each mobile computer).
Kit, Screen Cleaner Wipes	345-065-101	Includes 24 pre-moistened, non-abrasive, non-streaking 101.6 mm x 177.8 mm (4 in x 7 in) wipes.
Kit, Screen Protector (10/pk) 	346-069-107	Contains ten (10) self-adhesive screen protectors, 88.9 mm (3.5 in).
Kit, Screen Protector (25/pk) 	346-069-207	Contains twenty-five (25) self-adhesive screen protectors, 88.9 mm (3.5 in).

Mass Storage


PRODUCT NAME	SKU	DESCRIPTION
Micro SD Card, 1 GB	856-065-004	Industrial-grade Micro SD card for reliable performance in all 70/75 Series operating environments.
Micro SD Card, 2 GB	856-065-005	Industrial-grade Micro SD card for reliable performance in all 70/75 Series operating environments.
Micro SD Card, 4 GB	856-065-006	Industrial-grade Micro SD card for reliable performance in all 70/75 Series operating environments.

FlexDock

PRODUCT NAME	SKU	DESCRIPTION
Desktop Dock CN70/CN70e/CN75/CN75e No Power Cord CN70/CN70e/CN75/CN75e NA Power Cord CK70/CK71/CK75 No Power Cord CK70/CK71/CK75 NA Power Cord 	DX1A01A20 DX1A01A10 DX1A02B20 DX1A02B10	Accommodates one mobile computer and one auxiliary pack charger, capable of supporting two battery packs. Provides USB Host and Client connectivity. Includes power supply. North American customers should order configuration that includes NA Power Cord. Supports USB cable (236-209-001) via USB Client port for connection to Host PC. Supports optional Ethernet module (871-238-011) or Analog Modem module (871-238-002) via USB Host port. Charges mobile computer in less than 4 hours (typical); up to 6 hours for fully discharged batteries.
Cable Assy, USB-A to USBMicroB, 1 M (39.4 in) 	236-209-001	Provides USB Client connectivity between Desktop Dock and Host PC.
Ethernet Adapter, FlexDock Desktop 	871-238-011	Attaches to USB Host port on FlexDock Desktop to provide Ethernet connectivity.
Modem Adapter, FlexDock Desktop 	871-238-002	Attaches to USB Host port on FlexDock Desktop to provide analog modem communications.

PRODUCT NAME	SKU	DESCRIPTION
Dual Dock Ethernet CN70/CN70e/CN75/CN75e No Power Cord CN70/CN70e/CN75/CN75e NA Power Cord CK70/CK71/CK75 No Power Cord CK70/CK71/CK75 NA Power Cord Dual Dock Charge Only CN70/CN70e/CN75/CN75e No Power Cord CN70/CN70e/CN75/CN75e NA Power Cord CK70/CK71/CK75 No Power Cord CK70/CK71/CK75 NA Power Cord	DX2A11120 DX2A11110 DX2A12220 DX2A12210 DX2A21120 DX2A21110 DX2A22220 DX2A22210	Accommodates two mobile computers. Includes power supply. North American customers should order configuration that includes NA Power Cord. Optional 100Base-T Ethernet connectivity; provides two RJ45 jacks for upstream connections and downstream “daisy-chain” connections of up to 10 docks. Charges mobile computer in less than 4 hours (typical); up to 6 hours for fully discharged batteries.
		
Quad Dock Ethernet CN70/CN70e/CN75/CN75e No Power Cord CN70/CN70e/CN75/CN75e NA Power Cord CK70/CK71/CK75 No Power Cord CK70/CK71/CK75 NA Power Cord Quad Dock Charge Only CN70/CN70e/CN75/CN75e No Power Cord CN70/CN70e/CN75/CN75e NA Power Cord CK70/CK71/CK75 No Power Cord CK70/CK71/CK75 NA Power Cord	DX4A1111100 DX4A1111110 DX4A1222200 DX4A1222210 DX4A2111100 DX4A2111110 DX4A2222200 DX4A2222210	Accommodates four mobile computers. Includes power supply. North American customers should order configuration that includes NA Power Cord. Optional 100Base-T Ethernet connectivity; provides two RJ45 jacks for upstream connections and downstream “daisy-chain” connections of up to 10 docks. Charges mobile computer in less than 4 hours (typical); up to 6 hours for fully discharged batteries.
		

PRODUCT NAME	SKU	DESCRIPTION
4-Position Battery Charger CN70/CN70e/CN75/CN75e No Power Cord CN70/CN70e/CN75/CN75e NA Power Cord CK70/CK71/CK75 No Power Cord CK70/CK71/CK75 NA Power Cord	DX2A2AA20 DX2A2AA10 DX2A2BB20 DX2A2BB10	Accommodates two auxiliary pack charger cups, capable of supporting four battery packs. Includes power supply. North American customers should order configuration that includes NA Power Cord. Charges battery packs in 4 hours or less (typical); up to 6 hours for fully discharged batteries.
		
8-Position Battery Charger CN70/CN70e/CN75/CN75e No Power Cord CN70/CN70e/CN75/CN75e NA Power Cord CK70/CK71/CK75 No Power Cord CK70/CK71/CK75 NA Power Cord	DX4A2AAAA00 DX4A2AAAA10 DX4A2BBBB00 DX4A2BBBB10	Accommodates four auxiliary pack charger cups, capable of supporting eight battery packs. Includes power supply. North American customers should order configuration that includes NA Power Cord. Charges battery packs in 4 hours or less (typical); up to 6 hours for fully discharged batteries.
		

PRODUCT NAME	SKU	DESCRIPTION
Full-Page Printer Upgrade Kit, CN70/CN70e/CN75/CN75e 	203-966-001 203-967-001	682X series upgrade kits for CN70/CN70e/CN75/CN75e mobile computer. Pairing with mobile computer via Bluetooth or optional serial hardwired interface. Not compatible with Scan Handle, Magnetic Stripe Reader, or Snap-On Adapters.
Workboard Printer, CN70/CN70e/CN75/CN75e 	PW50A050101 PW50A050102	A 101.6 mm (4 in) direct thermal receipt printer specifically designed to retain and charge the mobile computer. DEX, Mag Stripe, Smart Card capable. Pairing with mobile computer via Bluetooth interface. Requires separate battery (318-026-001) for stand-alone operation. Not compatible with Scan Handle, Magnetic Stripe Reader, or Snap-On Adapters.
Workboard Printer Vehicle Docks, CN70/CN70e/CN75/CN75e 	225-777-001 225-778-001	PW50 Vehicle Mounting Docks for CN70/CN70e/CN75/CN75e mobile computer. Docks provide secure mounting and charging of both printer and mobile computer.

For more information
www.honeywellaidc.com
Honeywell Safety and Productivity Solutions

9680 Old Bailes Road
 Fort Mill, SC 29707
 800-582-4263
www.honeywell.com

Bluetooth is a trademark or registered trademark of Bluetooth SG, Inc. in the United States and/or other countries.

All other trademarks are the property of their respective owners.

70/75 Series Accessories Guide | Rev H | 04/18
 © 2018 Honeywell International Inc.

Honeywell