

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2018
© COPYRIGHT 2018 BY TE CONNECTIVITY ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE PER ECO-19-003803	12MAR2019	JAB	NLE
	A1	REVISED PER ECN-23-201433	24MAR2023	SR	AP




KEY CODE A
SCALE 4:1




KEY CODE B
SCALE 4:1




KEY CODE C
SCALE 4:1




KEY CODE D
SCALE 4:1




KEY CODE E
SCALE 4:1




KEY CODE F
SCALE 4:1




KEY CODE G
SCALE 4:1




KEY CODE H
SCALE 4:1




KEY CODE I
SCALE 4:1




KEY CODE K
SCALE 4:1




KEY CODE L
SCALE 4:1




KEY CODE M
SCALE 4:1




KEY CODE N
SCALE 4:1




KEY CODE Z
SCALE 4:1



ISOMETRIC VIEW
SCALE 3:1



SCALE 5:1



SCALE 5:1

WATER BLUE	Z	2-2307361-0
PASTEL GREEN	N	1-2307361-3
PASTEL ORANGE	M	1-2307361-2
CARMINE RED	L	1-2307361-1
CURRY	K	1-2307361-0
BEIGE	I	2307361-9
HEATHER VIOLET	H	2307361-8
BLUE GREY	G	2307361-7
NUT BROWN	F	2307361-6
LEAF GREEN	E	2307361-5
CLARET VIOLET	D	2307361-4
SIGNAL BLUE	C	2307361-3
CREAM	B	2307361-2
JET BLACK	A	2307361-1
COLOR	KEY CODE	PART NUMBER
OUTER HOUSING		

1. OUTER HOUSING: PBT, COLOR - SEE TABLE.
   CPA: PBT, RED.
2. CPA LOCATED IN THE PRE-LATCHED POSITION.
3. CLIP SLOT PER SAE/USCAR-18, EWCAP-005-7.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL 1

FINISH - -

DWN D.J.HARDY 27JAN2017
CHK N.L.EVANS 02FEB2017
APVD N.F.SCHROLL 02FEB2017
PRODUCT SPEC -
APPLICATION SPEC 114-32145
WEIGHT -

TE Connectivity

NAME FEMALE HOUSING ASSEMBLY, 180 DEGREE, CLIP SLOT, 1 POSITION, SEALED, AUTOMATED FAKRA

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2307361	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV A1

4805 (3/13)

Downloaded from Arrow.com.