



Part Number : [2018450020](#)

Product Description : MultiCat High-Power Plug Terminal, Gold over Nickel Phosphorus Plating, 14-12 AWG,

Series Number : 201845

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : FPG001P204



Documents and Resources

Drawings

[2018450020 sd.pdf](#)

[2018460001-PK.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2009140003-AS-000.pdf](#)

[2018400000-AS-000.pdf](#)

[2009140003-000.pdf](#)


[2018400000-PS-000.pdf](#)

[2009140003-TS-000.pdf](#)

[2018400000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 3; 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-

	DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	201845
Description	MultiCat High-Power Plug Terminal, Gold over Nickel Phosphorus Plating, 14-12 AWG,
Application	Power, Wire-to-Wire
Product Name	MultiCat
UPC	889056747301

Electrical

Current - Maximum per Contact	26.0A
Voltage - Maximum	1000V AC

Physical

Durability (mating cycles max)	500
--------------------------------	-----

Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel Phosphorus
Material - Plating Termination	Gold
Net Weight	2.098/g
Packaging Type	Bag
Plating min - Mating	0.100µm
Plating min - Termination	0.200µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.92-3.40mm
Wire Size (AWG)	12, 14
Wire Size mm ²	2.08-3.31

Mates With / Use With

Use with Part(s)

Description	Part Number
MultiCat High-Power Circular Plug Housings	<u>200914</u>
MultiCat High-Power Inline Plug Housings	<u>201840</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for MultiCat Machined High-Power Contact, 18-8 AWG	<u>2002182300</u>
Extraction Tool for MultiCat High-Power Crimp Terminals, 18-8 AWG	<u>2002220200</u>

This document was generated on May 14, 2026