




+ CONNECTORS

PCB D-SUB CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
Centronics,RCPT 36P,R/A,PB
CHAMP | CHAMP

1-1734044-1
TE Internal Number: 1-1734044-1

- EU RoHS Compliant
- EU ELV Compliant
- Connector Style Receptacle
- Number of Positions 36
- Centerline (Pitch) 2.16 mm [.085 in]
- Number of Rows 2
- Row-to-Row Spacing .085

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings
RECEPTACLE ASSEMBLY, 36P RIGHT ANGLE, CENTRONICS.
PDF
English

CAD Files
3D PDF
PDF
3D
Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Connector Style Receptacle
- Row-to-Row Spacing .085
- Profile Standard
- PCB Mounting Orientation Right Angle
- Connector & Contact Terminates To Printed Circuit Board
- Product Type Connector
- Orientation Standard
- Grounded No
- Shielded Yes

Configuration Features

- Number of Positions 36
- Number of Rows 2
- Preloaded Yes

Body Features

- Shield Plating Material Nickel
- Shell Material Steel
- Shield Material Steel
- Shell Plating Material Nickel
- Color Black

Contact Features

- Solder Tail Contact Plating Material Tin
- Contact Mating Area Plating Material Gold
- Contact Mating Area Plating Thickness (µin) 15
- Contact Base Material Copper Alloy

Mechanical Attachment

Panel Mount Retention With
PCB Mounting Style Through Hole
PCB Mount Retention With
PCB Mount Retention Type Boardlocks
Mating Connector Lock With
Mating Connector Lock Type Bail Lock, Rivet, 4/40 UNC
Bail-Clip Material Stainless Steel
Boardlock Material Brass
Panel Attachment Style Rear Mount
Mounting Hole Diameter (mm) 3.2
Boardlock Plating Material Tin

Housing Features

Centerline (Pitch) 2.16 mm [.085 in]
Housing Color Black
Housing Material Thermoplastic

Dimensions

PCB Thickness (Recommended) 1.57 mm [.062 in]

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 12
Packaging Method Piece/Tray

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF