

**Part Number :** [1300990104](#)

**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 15.88-19.05mm (.625-.750"), Stainless Steel Mesh and Nylon Compression Nut

**Series Number :** 130099

**Status :** Not Recommended For New Design

**Product Category :** Cable Grips

**Engineering Part Number :** 5542M



---

## Documents and Resources

### Drawings

[1300990104\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

|              |                                                                                                                                                             |
|--------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Status       | Not Recommended For New Design                                                                                                                              |
| Category     | Cable Grips                                                                                                                                                 |
| Series       | 130099                                                                                                                                                      |
| Description  | MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 15.88-19.05mm (.625-.750"), Stainless Steel Mesh and Nylon Compression Nut |
| NEMA Rating  | NEMA 3R                                                                                                                                                     |
| Product Name | MAX-LOC                                                                                                                                                     |
| Type         | Strain Relief Grip                                                                                                                                          |
| UPC          | 78678855420                                                                                                                                                 |

### Agency

|     |         |
|-----|---------|
| CSA | LR32159 |
|-----|---------|

### Physical

|                            |                            |
|----------------------------|----------------------------|
| Approximate Break Strength | N/A                        |
| Bale Length                | N/A                        |
| Body Style                 | Straight                   |
| Cable Diameter             | 15.88-19.05mm (.625-.750") |
| Color - Grommet            | Orange                     |
| Eye Type                   | N/A                        |
| Gender                     | Male                       |
| Material - Body            | Nylon                      |
| Material - Grip            | Stainless Steel            |
| Mesh Length                | N/A                        |
| Number of Holes            | 1                          |
| O-Ring                     | No                         |
| Thread Size                | 3/4" NPT                   |

### Mates With / Use With

**Use with Part(s)**

| Description                                     | Part Number       |
|-------------------------------------------------|-------------------|
| MAX-LOC Lock Nut 3/4" NPT                       | <u>1300990144</u> |
| MAX-LOC Gasket Sealing Ring,<br>3/4" NPT, Black | <u>1300990150</u> |
| MAX-LOC O-Ring, 3/4" NPT                        | <u>1301800333</u> |

---

This document was generated on Aug 31, 2026