




Part Number : [2160000200](#)

Product Description : NearStack HD Right-Angle-to-NearStack HD Right-Angle Cable Assembly, Pull Tab, Without Expando, 56 Circuits, 18 Differential Pair, 200.00mm

Series Number : 216000

Status : Active

Product Category : High-Speed I/O Cable Assemblies



Documents and Resources

Drawings

[2160000200 sd.pdf](#)

[2160000001-PK.pdf](#)


Specifications

[2159800001-AS-000.pdf](#)

[2159800001-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	216000
Description	NearStack HD Right-Angle-to-NearStack HD Right-Angle Cable Assembly, Pull Tab, Without Expando, 56 Circuits, 18 Differential Pair, 200.00mm
Assembly Configuration	Dual Ended Connectors
Connector to Connector	NearStack HD-to-NearStack HD
Product Name	NearStack HD
Type	Internal
UPC	195842815223

Agency

CSA	LR19980
UL	E29179

Electrical

Data Rate	64 Gbps (PAM-4)
Voltage - Maximum	29.9V AC (RMS)/DC

Physical

Cable Bundling	None
Cable Length	200.00mm

Circuits (Loaded)	56
Circuits (maximum)	56
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle/Receptacle
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	17.546/g
Number of Pairs	18
Orientation	Right-Angle-to-Right-Angle
Release Style	Pull Tab
Single Ended	No
Wire/Cable Type	Twinax

Mates With / Use With

Mates with Part(s)

Description	Part Number
NearStack HD Connectors	<u>215980</u>

This document was generated on Apr 20, 2026