

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories

→ End Sections

## General Information

<b>Extended Product Type:</b>	ES4
<b>Product ID:</b>	1SNK505910R0000
<b>EAN:</b>	3472599097230
<b>Catalog Description:</b>	ES4 End Section - Dark Grey
<b>Long Description:</b>	- Unique dark grey color that fits all terminal blocks colours and ease the identification of circuits within your terminal block assemblies, - Compatible with feed-through, ground and disconnect screw clamp terminal blocks.

## Ordering

<b>Color:</b>	Dark Grey
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	39269097

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160022D0201
<b>Instructions and Manuals:</b>	1SNK160027C0201

## Dimensions

<b>Product Net Width:</b>	2.2 mm
<b>Product Net Height:</b>	50.9 mm
<b>Product Net Length:</b>	33.7 mm
<b>Product Net Depth / Length:</b>	33.7 mm
<b>Product Net Weight:</b>	2.2 g

## Technical

<b>Spacing:</b>	2.2 mm
<b>Function:</b>	End Sections
<b>Pollution Degree:</b>	3
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715

<b>Suitable For:</b>	ZS10
	ZS10-PE
	ZS10-S
	ZS10-SP
	ZS16
	ZS16-PE
	ZS25
	ZS25-PE
	ZS4
	ZS4-PE
	ZS4-S
	ZS4-SP
	ZS4-SP-T2
	ZS4-S-T
	ZS6
	ZS6-PE
	ZS6-S

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V0
--	----

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C
	Storage -55 ... +110 °C
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	Compliant
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>Environmental Information:</b>	1SND220077E1000
<b>Instructions and Manuals:</b>	1SNK160027C0201
<b>RoHS Information:</b>	1SND230497F0203

## Classifications

<b>Object Classification Code:</b>	X
<b>E-nummer:</b>	2925143
<b>ETIM 4:</b>	EC000886 - Endplate and partition plate for terminal block
<b>ETIM 5:</b>	EC000886 - Endplate and partition plate for terminal block
<b>ETIM 6:</b>	EC000886 - Endplate and partition plate for terminal block

## Container Information

<b>Package Level 1 Units:</b>	20 piece
<b>Package Level 1 Width:</b>	158 mm
<b>Package Level 1 Depth / Length:</b>	243 mm

Package Level 1 Gross Weight:	0.044 kg
Package Level 1 EAN:	3472599097230
Package Level 2 Units:	4000 piece
Product Packing Type:	Bag

