454/7 HF Set 2 Screwdriver set T-handle Hex-Plus screwdrivers with holding function, 7 pieces



EAN:	4013288221742	**Size:**	280x220x75 mm
Part number:	05023453001	**Weight:**	1379 g
Article number:	454/7 HF Set 2	**Country of origin:**	CZ
		Customs tariff number:	82054000

- T-handle screwdriver for the transmission of particularly high tightening and loosening torque
- Ergonomic 2-component handle with finger handle recesses and pleasant surface feel for very high power transmission and fatigue-free working
- Take it easy tool finder: colour coding according to profile and size
- With additional short arm for the transmission of extremely high torques due to the leverage of the long arm
- With holding function (HF) on the long arm to securely hold the screw on the tool
- Including metal rack; the rack can be placed upright or hung on the tool wall.

T-handle screwdriver: The ideal handle shape allows the transmission of particularly high tightening and loosening torque. The ergonomic shape of the handle fills the palm of the hand well, the fingers lie safely in the soft rounded handle recesses. The whole hand makes contact with the handle and friction losses between the hand and the handle are avoided. With holding function to securely hold the hexagon socket screw on the tool. Special surface treatment of the blades for high corrosion protection and optimum fitting accuracy in the screw. Including metal rack for storage. The rack can be placed on the workbench or hung on the tool wall.

Web link
https://www.wera.de/en/05023453001

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Downloaded from Arrow.com.



Ergonomic 2-component T-handle



The ergonomically shaped 2-component T-handle with finger recesses and pleasant surface facilitates very high power transmission and fatigue-free working.

Holding Function (HF) for hexagon socket screws




A spring loaded ball ensures the hexagon socket screw to be clamped on the tool tip. Especially helpful in hard to reach areas where you can not use your other hand to hold the screw.

Second arm



The additional short arm, which emerges laterally from the handle, allows the transmission of extremely high torques by using the long arm as a lever.

High torque transfer




By using the blade as an extension of your lower arm you can transfer particularly high torque.

Corrosion protection and fitting accuracy



Due to the special surface treatment, the blades receive a high level of corrosion protection. The optimum fitting accuracy of the screw is also guaranteed.

Take it easy Tool Finder



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.

With useful metal rack



Including metal rack for clearly arranged storage in the workshop. The rack can be placed upright or hung on the tool wall. The T-handle screwdrivers can be easily removed from the rack due to the angle of the rack when mounting it on the wall. The T-handles will not be pinched by the wall.

Web link
https://www.wera.de/en/05023453001

Wera - 454/7 HF Set 2
05023453001 - 4013288221742

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de


Downloaded from Arrow.com.

454/7 HF Set 2 Screwdriver set T-handle Hex-Plus screwdrivers with holding function, 7 pieces

Set contents:

454 T-handle hexagon screwdriver Hex-Plus, 2.5 x 100 mm

05023332001	1x	2.5 x 100 mm



454 HF T-handle hexagon screwdriver Hex-Plus with holding function, 3 x 100 mm

05023334001	1x	3 x 100 mm
05023338001	1x	4 x 100 mm
05023343001	1x	5 x 150 mm
05023347001	1x	6 x 150 mm
05023353001	1x	8 x 200 mm
05023355001	1x	10 x 200 mm



9604 Metal rack for T-handle screwdrivers, 214 x 78 mm

05136424001	1x	214 x 78 mm



Web link
https://www.wera.de/en/05023453001

Wera - 454/7 HF Set 2
05023453001 - 4013288221742

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Downloaded from Arrow.com.