



[My Cart](#) |



[My Part Lists](#) |

[Sign In/Register](#) |



[English \(Change\)](#)

Have a Question?

Chat with a Product
Information Specialist



What can we help you find?



[Products](#)

[Industries](#)

[Resources](#)

[About TE](#)

[My Account](#)

[Innovation](#)

[Support Center](#)

[Home](#) > [Products](#) > [D-Subminiature Connectors](#) > [Product Feature Selector](#) > [Product Details](#)

167501-2 Product Details

[Share](#)

[Print](#)

[Email](#)



167501-2

TE Internal Number: 167501-2

Active

[View 3D PDF](#)

Hardware (AMPLIMITE)



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Accessory Type = Female Screwlock Assembly Kit
- Tin Body Finish
- Thread Size = 4-40
- Thread Length = 7.90 mm
- Screwlock Style = Screwlock With Lockwasher and Hex Nut

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [amplimite, kit, female screwlock assembly 4-40 unc](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version G)
- [3D Model](#) (IGES, Version G)
- [3D Model](#) (STEP, Version G)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Accessory Type = Female Screwlock Assembly Kit
- [Thread Size](#) = 4-40

Body Features:

- [Body Finish](#) = Tin
- [Thread Length \(mm \[in\]\)](#) = 7.90 [0.311]
- Screwlock Style = Screwlock With Lockwasher and Hex Nut
- Mating Thread Size = 4-40
- Body Material = Steel

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:

- [Packaging Method](#) = Bulk

Other:

- Brand = AMP
- Comment = For Rear Panel Mount.

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

