

## M12 Y-cod 8-pol st/st m/m PUR 5.0m



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 21 34 262 6840 050  |
| Specification      | M12 Y-cod 8-pol st/st m/m PUR 5.0m  |
| HARTING eCatalogue | <a href="https://harting.com/21342626840050">https://harting.com/21342626840050</a> |

### Identification

|               |                               |
|---------------|-------------------------------|
| Category      | System cabling                |
| Series        | Circular connectors M12       |
| Element       | Cable assemblies              |
| Specification | Pre-assembled on both sides   |
| Connector 1   | M12 Y-coding<br>Male Straight |
| Connector 2   | M12 Y-coding<br>Male Straight |
| Type of cable | Copper cable (round)          |

### Version

|                 |                        |
|-----------------|------------------------|
| Cable length    | 5 m                    |
| Number of cores | 8                      |
| Core structure  | 4x AWG20 + 1x 4x AWG26 |
| Coding          | Y-coding               |

### Technical characteristics

|                      |                |
|----------------------|----------------|
| Limiting temperature | -25 ... +80 °C |
|----------------------|----------------|

### Material properties

|                  |  |
|------------------|--|
| Material (cable) | PUR (polyurethane)                                     |
| Colour (cable)   | Green  |
| RoHS             | compliant with exemption                               |
| RoHS exemptions  | 6(c): Copper alloy containing up to 4 % lead by weight |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| ELV status                           | compliant with exemption             |
| China RoHS                           | 50                                   |
| REACH Annex XVII substances          | Not contained                        |
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | 760691ac-b4d2-427c-9996-5886190b813b |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead<br>Nickel                       |

## Specifications and approvals

|           |    |
|-----------|----|
| Approvals | CE |
|-----------|----|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Country of origin              | Czechia                                      |
| European customs tariff number | 85444995                                     |
| GTIN                           | 5713140282636                                |
| eCl@ss                         | 27060390 Ready-made data cable (unspecified) |
| ETIM                           | EC002599                                     |
| UNSPSC 24.0                    | 26121600                                     |