


44A1131-24-4/5/6-9 Product Details

 Share  Print  Email



 Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

44A1131-24-4/5/6-9

44A1131-24-4/5/6-9 

TE Internal Number: 3865873001

Product Highlights [View All](#)

- Cable Type = Spec 44
- Wire Source = United Kingdom, United States
- Cable Style = Round Braid Shielded and Jacketed
- Wire Size (AWG/CM) = 22 AWG
- Voltage Rating = 600 VAC

Pricing & Availability 

Request Sample 

Add to My Part List 

Buy Product through Distributor 

 Feedback

Documents

Features

Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Cable Type 	Spec 44
Cable Style	Round Braid Shielded and Jacketed

Electrical Characteristics	
Voltage Rating (VAC)	600

Dimensions	
Conductor Outer Diameter (mm [in])	0.64 [0.025] 
Shield (Screen) Diameter (mm [in])	2.74 [0.108]

Body Features	
Wire Size (AWG/CM)	22 AWG
Cable Jacket Color	White
Conductor Type	Tin-Coated Copper
Wire Color	Yellow, Green, Blue
Nominal Outside Diameter (mm [in])	3.28 [0.129]
Wire Diameter (mm [in])	1.02 [0.040]
Shield Size	36 AWG
Shield Material	Tin Plated Copper

Configuration Features	
Number of Conductors	3

Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant 

Conditions for Usage	
Temperature Range (°C)	-65 – +150
Wire Size - Details	24 AWG 0.24 mm², 0.00037 in², 19 x 36 AWG

Operation/Application	
Application	General Purpose, General Purpose - Light Weight

Packaging Features	
Wire Source	United Kingdom, United States

Other	
Brand	Raychem
Node Classification	Multicore Cable

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

