



- NOTES:
1. ALL PARTS TO BE BULK PACKED.
 2. CONTACTS ASSEMBLED INTO CONNECTOR.
 3. BACK WELL FILLED WITH EPOXY.
 4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH A TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.
 5. PC TAIL LENGTH OPTIONS:
 - STANDARD (SHORT) TAIL = 0.114in [W4281-1XPG-3ES]
 - INTERMEDIATE = 0.202in [W4291-1XPG-3ES]
 - LONG = 0.257in [W4292-1XPG-3ES]

ASS'Y P/N	CONTACTS	HOLE POS. CLOSED
W4291-10PG-3ES	10 - #20	11, 12
W4291-11PG-3ES	11 - #20	12
W4291-12PG-3ES	12 - #20	NONE
W4291-1XPG-3ES		


NO. OF CONTACTS




FACE VIEW
W4291-10PG-3ES
10-POS.



FACE VIEW
W4291-11PG-3ES
11-POS.




FACE VIEW
W4291-12PG-3ES
12-POS.



MAT'L: UV THERMOPLASTIC, BLACK


MAT'L: RUBBER, BLACK

13/16-27 UNS-2A MOD. THREAD





EPOXY FILLED
SEE NOTE 3


PANEL INSERT, PIN
MAT'L: UV THERMOPLASTIC, BLACK



PC TAIL VIEW
W4291-10PG-3ES - 10-POS. (11&12 CLOSED)
W4291-11PG-3ES - 11-POS. (12 CLOSED)
W4291-12PG-3ES - 12-POS. (ALL OPEN)



PC TAIL LAYOUT




RECOMMENDED
PANEL CUTOUT
STANDARD MULTI-CON-X

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1		
REV.	INIT.	DATE	DESCRIPTION		
	PAK	10/22/14	ORIG. DRAWN BY:	DATE:	 601 E. WILDWOOD VILLA PARK, IL 60181
			CHECKED BY:		
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			APPROVED BY:		TITLE: PANEL PIN, W/ EPOXY 12-POS., #20 PC TAIL, INTERMEDIATE MULTI-CON-X, E-KEY, WEATHER RESISTANT CUSTOMER: STANDARD PRODUCT
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 C = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SCALE NTS	SIZE B	
			SHEET 1 OF 1	DIRECTORY: SLW	PART NUMBER: W4291-1XPG-3ES
					REV A