

Bosch Worldwide (http://www.bosch.com)
EN | DE (https://www.bosch-connectors.com/view?p_p_auth=xroy8oI1&p_p_id=49&p_p_lifecycle=1&p_p_state=normal&p_p_mode=view&_49_struts_action=%2Fview%2Fview%2Fproduct%2FBTC-BTL-4-8-6-3-Single-Wire-Seal-%25C3%2598-3-4-%25C3%2598-3-7-FLR-Blue%2F1928301086&_49_language=de-DE)
Login / Register

Bosch Connectors (https://www.bosch-connectors.com/view?)

p_p_auth=xroy8oI1&p_p_id=49&p_p_lifecycle=1&p_p_state=normal&p_p_mode=view&_49_struts_action=%2Fmy_sites%2Fview%2Fview%2Fproduct%2FBTC-BTL-4-8-6-3-Single-Wire-Seal-%25C3%2598-3-4-%25C3%2598-3-7-FLR-Blue%2F1928301086&_49_language=de-DE)

 **BOSCH** (https://www.bosch-connectors.com/view?)
created for file
p_auth=xroy8oI1&p_p_id=49&p_p_lifecycle=1&p_p_state=normal&p_p_mode=view&_49_struts_action=%2Fmy_sites%2Fview%2Fview%2Fproduct%2FBTC-BTL-4-8-6-3-Single-Wire-Seal-%25C3%2598-3-4-%25C3%2598-3-7-FLR-Blue%2F1928301086&_49_language=de-DE)

BTC / BTL 4.8 / 6.3 / Single Wire Seal / Ø 3.4 - Ø 3.7 (FLR) / Blue [Back to Catalog](#)



1 928 301 086
Status Active
Selected Technical Details

Packaging Unit 4000 piece

Colour

blue

[Full Technical Details](#)

Downloads

Offer Drawing (Part)

<https://gs-gsconnector-1928A00431-us.resource.bosch.com/media/1928A00431-DEEN%20AGZ%20001%2006%201%20%20SAP-Status%2040%20%20Labor%20F15%20%20Change%20F1928499398>

Technical Data	
Manufacturer	Bosch
Packing Unit	4000 pc.
Product Type	Single Wire Seal
Colour	blue
Length	9.00 mm
Width	9.00 mm
Height	7.80 mm
Temperature Range, Min.	-40 °C
Temperature Range, Max.	125 °C

[Back to Catalog](#)

- APPLICATIONS**
- Passenger Car (https://www.bosch-connectors.com/catalog?vehicle=passenger-car)
- Commercial Vehicle (https://www.bosch-connectors.com/catalog?vehicle=commercial)
- Two-Wheeler (https://www.bosch-connectors.com/catalog?vehicle=two-wheeler)