

**Part Number :** [395305003](#)  
**Product Description :** 5.08mm Pitch Eurostyle  
Horizontal Plug, Green Housing, 3 Circuits  
**Series Number :** 39530  
**Status :** Active  
**Product Category :** Terminal Blocks and Barrier  
Strip

---

## Documents and Resources

### Drawings

[395305003\\_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-39500-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39530
Description	5.08mm Pitch Eurostyle Horizontal Plug, Green Housing, 3 Circuits
Application	Wire-to-Board
Component Type	Plug
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350535663

### Agency

UL	E48521
----	--------

### Electrical

Current - Maximum per Contact	18.0A
Voltage - Maximum	300V

### Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Green

Entry Angle	Vertical
Lock to Mating Part	Yes
Net Weight	0.010/mg
Number of Rows	1
Orientation	N/A
Panel Mount	No
PCB Retention	N/A
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	12, 14, 16, 18, 20, 22, 24, 26
Wire Size mm <sup>2</sup>	0.13-3.31

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
5.08mm Pitch Eurostyle Vertical PCB Headers	<u><a href="#">39531</a></u>
5.08mm Pitch Eurostyle Horizontal PCB Headers	<u><a href="#">39532</a></u>
5.08mm Pitch Eurostyle Dual Level PCB Headers	<u><a href="#">39538</a></u>
Mates With	Most 5.08mm Pitch Industry Standard PCB Headers

---

This document was generated on Apr 15, 2026