

44AM1121-20-9/96-9CS2275 Product Details

 Share  Print  Email



 Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

44AM1121-20-9/96-9CS2275
44AM1121-20-9/96-9CS2275 (M27500-20ML2T08)
 TE Internal Number: 731235-000

- Product Highlights [View All](#)
- Cable Type = Spec 44
 - Wire Source = United States
 - Cable Style = Jacketed, Round-Braid Shielded
 - Wire Size (AWG/CM) = 20 AWG
 - Voltage Rating = 600 VAC

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

 Feedback

Documents

Features

Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Cable Type 	Spec 44
Cable Style 	Jacketed, Round-Braid Shielded
Electrical Characteristics	
Voltage Rating (VAC)	600
Dimensions	
Conductor Outer Diameter (mm [in])	1.01 [0.040]
Shield (Screen) Diameter (mm [in])	3.35 [0.132]
Body Features	
Wire Size (AWG/CM)	20 AWG
Cable Jacket Color	White
Conductor Type	Tin-Coated Copper
Wire Color	White, White w/ Blue Stripe
Nominal Outside Diameter (mm [in])	3.76 [0.148]
Wire Diameter (mm [in])	1.40 [0.055]
Configuration Features	
Number of Conductors	Twisted Pair

Industry Standards	
Government/Industry Qualification	Yes
Government/Industry Part Number	M27500-20ML2T08
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Converted to comply with RoHS directive
Conditions for Usage	
Temperature Range (°C)	-65 – +150
Wire Size - Details	20 AWG 0.62 mm², 0.00095 in², 19 x 32 AWG
Operation/Application	
Application	General Purpose - Light Weight
Packaging Features	
Wire Source	United States
Other	
Brand	Raychem
Node Classification	Twisted Pair Cable

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE

Investors

News Room

Supplier Portal

Careers

Terms & Conditions

Privacy Policy

Global Accessibility Statement

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed



