

PATG 5/30 - Conductor marker carrier



0822482

<https://www.phoenixcontact.com/us/products/0822482>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, transparent, unmarked, cable diameter range: 10 ... 14 mm, mounting type: slide-on, text field height: 4 mm, text field width: 30 mm

Your advantages

- The corresponding UC-WMT ..., US-WMT ..., and EMT ... insert labels are used for marking
- These conductor marking systems consist of marker carriers and insert labels
- The PATG ... collar is a captive marker carrier
- Can be used to mark conductors with a diameter of 0.6 mm ... 50 mm

Commercial data

Item number	0822482
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	BG12
Product key	BG221A
GTIN	4046356326216
Weight per piece (including packing)	1.456 g
Weight per piece (excluding packing)	1.456 g
Customs tariff number	39269097
Country of origin	DE

PATG 5/30 - Conductor marker carrier



0822482

<https://www.phoenixcontact.com/us/products/0822482>

Technical data

Product properties

Product type	Marker carrier cable
Type	Profile

Dimensions

Width	30 mm
Height	15.4 mm
Depth	16.1 mm

External dimensions

Outside diameter	10 mm ... 14 mm
------------------	-----------------

Text field

Text field width	30 mm
Text field height	4 mm

Material specifications

RoHS compliant	yes
Color	transparent
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Cable/line

External cable diameter	10 mm ... 14 mm
-------------------------	-----------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	slide-on
---------------	----------

PATG 5/30 - Conductor marker carrier



0822482

<https://www.phoenixcontact.com/us/products/0822482>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PATG 5/30 - Conductor marker carrier



0822482
<https://www.phoenixcontact.com/us/products/0822482>

Environmental product compliance

EU RoHS		
Fulfills EU RoHS substance requirements		Yes, No exemptions
EU REACH SVHC		
REACH candidate substance (CAS No.)		No substance above 0.1 wt%
EF3.0 Climate Change		
CO2e kg		0.211 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com