

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see our [Privacy Statement](#).

[Don't show this message again](#)**Honeywell** | Sensing and ControlChoose Language  English

Search the entire website and product database

 Start Here ...

Search

[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)**GXE51A1B**([Home](#) : [Products](#) : [Active Product Family](#) 10-Oct-2006 : [Switches](#) : [MICRO SWITCH™](#) [Hazardous Location Switches](#) : [GXS](#))**Explosion-Proof Limit Switches Series GXS: Side Rotary; 1NC 1NO SPDT Snap Action; 5 m Cable**[click here to download Hi-Res image](#)

Actual product appearance may vary.

[Sales & Service](#)[Distributor Inventory](#)[Overview](#)[Specs](#)[Documentation](#)[Application Notes](#)**Product Specifications**

Availability	Europe; Asia-Pacific
Product Type	MICRO SWITCH™ Explosion-Proof Limit Switches
Actuator	Side Rotary
Lever Type	Roller - Standard
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	5 A (Thermal)
Supply Voltage	240 Vac
Housing Material	Zinc Die-Cast
Termination Type	5 m Cable
Housing Type	GXS
Series Name	GXS
Sealing	IP66
ATEX File #	KEVA 00 ATEX 2103 X
IEC Ex	Yes
Expected Mechanical Life	up to 2 Million
Operating Temperature	-25 °C to 75 °C [35 °F to 168 °F]
Comment	Bottom Exit Cable; Explosion Proof Construction EEx d IIC T6; EN50014, EN50018, IEC947-5-1, EN60947-5-1
Agency Approvals and Standards	ATEX (CE), IEC Ex
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Explosion-proof

Product SearchProduct Type: Industry: Search Term: ☐ New Products Only☐ Entire Product Catalog

Search

[Distributor Inventory](#)

Input part number for stock availability

Narrow Your Search**Modify Your Search****Products****Technology****Industries Served****My Links**[eCOM Login](#)**Literature and Media**[Data Sheets](#)**Contacts**[Customer Service](#)

- Request Access to eCOM
- Rep/AD Portal Login
- Rep/AD Portal Access Request
- Sample Request
- Digital U - HML Learning Hub Login
- Digital U - HML Learning Hub Access Request
- Limitless Microsite
- Supplier Microsite

- Videos
- Literature
- Literature Request
- White Papers
- Application Notes
- Application Demos
- CAD Renderings

- Technical Support
- Global Sales & Service
- Website Feedback

YouTube

Terms & Conditions

|

Privacy Statement

|

Site Map