


[Connectors](#) > [Automotive Connectors: Car, Truck, Bus, & Off-Road](#) > [Automotive Seals & Cavity Plugs](#)

CABLE SEAL HVA280 2P



✓ ACTIVE

HVA 280

TE Part # **2260703-1**TE Internal #: **2260703-1**Seal Type : **Cable Seal**Cable Insulation Diameter : **4.29 – 4.89 mm**
[.168 – .192 in]Material : **Silicone**Shore A Hardness : **30**Lubricant Content : **Yes** Add to List ▼[Similar Products](#)**ORDER SAMPLES****Compatible Parts & Tooling**

SHOP OUR DISTRIBUTORS

North America ▼

Request pricing, availability and customization options

CONTACT US

We are here to help!

Get in touch with our product experts.

**CHAT WITH US****EMAIL US****CALL US**

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

CABLE SEAL HVA280 2P

 [CABLE SEAL HVA280 2P](#) Japanese

CAD Files

3D PDF

 [3D_CVM_CVM_2260703-1_A.pdf](#) 3D

Customer View Model

 [ENG_CVM_CVM_2260703-1_A.2d_dxf.zip](#)

English

 [ENG_CVM_CVM_2260703-1_A.3d_igs.zip](#)

English

 [ENG_CVM_CVM_2260703-1_A.3d_stp.zip](#)

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.Product Type
FeaturesSeal Type : **Cable Seal**

Body Features

Material : **Silicone**Color : **Gray**

Dimensions	Cable Insulation Diameter : 4.29 – 4.89 mm [.168 – .192 in]
Packaging Features	Packaging Method : Bag Packaging Quantity : 1000
Other	Shore A Hardness : 30 Lubricant Content : Yes
Statement of Compliance	Statement of Compliance pdf

Compatible Parts

> [Contact Product Support](#)

Also in the Series

| [HVA 280](#)

Automotive
Connector Caps &
Covers (3)

Automotive
Connector EMC
Shielding (15)

Automotive Seals &
Cavity Plugs (7)

Automotive, Truck,
Bus, & Off-Road
Headers (25)

Customers Also Bought

TE Part # 2103171-1
SHIELD, CAP,
HVA280-2PHM

TE Part # 2103170-1
INNER HOUSING,
CAP, HVA280-2PHM

TE Part # 2103245-4
Inner Housing, Split
Hdr, Key D, HVA280

TE Part # 2103245-5
Inner Housing, Split
Hdr, Key E, HVA280

[Our Company](#)

[Events](#)

[TE News Center](#)

[Careers](#)

[Investors](#)

[Corporate Responsibility](#)

[Terms and Conditions of Sale](#)

[Distributors](#)

[Suppliers](#)



[Email or Call Us](#)



[Find Authorized Distributors](#)



[What's New on TE.com](#)



[Product FAQs](#)

[Select Country & Language](#)

[United States \(EN\)](#)

[Germany \(DE\)](#)

[China \(中文\)](#)

[Japan \(日本語\)](#)

[Find Your Country/Region](#) ▼

[Terms of Use](#)

[Privacy](#)

[Cookie Policy](#)

[Accessibility](#)

[Site Map](#)



© 2018 TE Connectivity. All Rights Reserved.