



**Part Number :** [08550102](#)

**Product Description :** KK 254 Crimp Terminal, 30-22 AWG, Bag, Selective Gold (Au), Nickel (Ni) Under Plating

**Series Number :** 2759

**Status :** Active

**Product Category :** Crimp Terminals

**Engineering Part Number :** 2759-(555)L

**Packaging Alternative :** [08550101](#) (Reel)



---

## Documents and Resources

### Drawings

[008550102\\_sd.pdf](#)

[PK-2759-001-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-10-07-001.pdf](#)


[50510002-PS-000.pdf](#)

[TS-10-07-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	2759
Description	KK 254 Crimp Terminal, 30-22 AWG, Bag, Selective Gold (Au), Nickel (Ni) Under Plating
Application	Signal, Wire-to-Board
Product Name	KK 254
UPC	800753745995

### Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.064/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.

Wire Size (AWG)	22, 24, 26, 28, 30
Wire Size mm <sup>2</sup>	N/A

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

### Mates With / Use With

#### Use with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	<u>2695</u>
KK 2.50mm Pitch Single Row Receptacle Housings	<u>5051</u>

---

### Application Tooling

#### Global

Description	Part Number
Extraction Tool for KK 2.54mm Terminals, 30-22 AWG	<u>11030022</u>
PremiumGrade Hand Crimp Tool for KK 2.54mm Crimp Terminals, 30-22 AWG	<u>638118200</u>
Insertion Tool for KK 2.54mm Terminals, 30-22 AWG	<u>638120000</u>

---

This document was generated on Dec 16, 2025