

Marker carriers - CARRIER-EMP (27X15) - 0827451

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker carriers, black, unlabeled, mounting type: screw, rivet, lettering field size: 27 x 15 mm

Your advantages

- ✓ CARRIER-EMP ... marker carriers are used in conjunction with UC-EMP .../US-EMP ... snap-in labels
- ✓ They are used to clearly identify devices and control cabinets
- ✓ They can be mounted using screws or rivets

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	80 pc
GTIN	 4 046356 440745
GTIN	4046356440745
Weight per Piece (excluding packing)	1.250 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	17 mm
Width (a)	30 mm
Height (c)	6 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

Marker carriers - CARRIER-EMP (27X15) - 0827451

Technical data

General

Color	black
Components	free from silicone and halogen
Material	PA
Flammability rating according to UL 94	V2
Mounting type	screw, rivet

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	27144075
eCl@ss 11.0	27281105
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 9.0	27144075

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC002248
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 19.0	39131504

Marker carriers - CARRIER-EMP (27X15) - 0827451

Accessories

Accessories

Device marking

Snap-in markers - UC-EMP (27X15) - 0825439



Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 8

Snap-in markers - UC-EMP (27X15) SR - 0825441



Snap-in markers, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 8

Snap-in markers - UC-EMP (27X15) YE - 0825440



Snap-in markers, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 8

Snap-in markers - US-EMP (27X15) - 0828777



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 27

Snap-in markers - US-EMP (27X15) SR - 0828849



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 27

Marker carriers - CARRIER-EMP (27X15) - 0827451

Accessories

Snap-in markers - US-EMP (27X15) YE - 0828848

Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 27
