

Honeywell Sensing and Control

Search



12TW2-10
(Home : Products : MICRO SWITCH™ Toggle Switches » TW » Other Switches » MICRO SWITCH™ Electromechanical Switches)

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6004)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (988)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1409)
- More...

new products**New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)**white papers**

- ▷ Wireless Switches Offer Unlimited Benefit
- ▷ Basic Switches Are Not Created Equal
- ▷ Applying Precision Switches
- ▷ Sensors for Medical Devices
- ▷ New Ways to Measure Torque
- ▷ Choosing Safety Switches
- ▷ Specifying Hour Meters

Need help?[Click here to contact us](#)

TW Series Toggle Switch, 2 pole, 3 position, H58 terminal, Locking Lever


Actual product appearance may vary.

[Sales & Service](#)[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Circuitry/Operating action



Product Type	MICRO SWITCH™ Toggle Switch
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vac to 115 Vac, 0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc
Circuitry	DPDT
Action	3 position
Mounting	Bushing 15/32 in
Termination	H58
Lever Type	Locking
UL/CSA	L117: 5 A at 125 Vac
Comment	Fine silver contacts
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TW

contacts

- ▷ Customer Service
- ▷ Technical Support
- ▷ Global Sales & Service
- ▷ View Site Demo
- ▷ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

[Meet Dr. Larry](#)**my links**

- ▷ Login to iCOM
- ▷ Login to Rep/AD Portal
- ▷ Login to Digital University

News Center

- ▷ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- ▷ HONEYWELL EXTENDS ITs TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- ▷ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▷ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- ▷ HONEYWELL INTRODUCES MICROPower OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

MICRO SWITCH
Anniversary site

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)